


TOLERANCING SYMBOL	JIS B 0021
STRAIGHTNESS	—
FLATNESS	▭
CIRCULARITY	○
CYLINDRICITY	⊗
LINE PROFILE	⤴
SURFACE PROFILE	⤴
PARALLELISM	∥
PERPENDICULARITY	⊥
ANGULARITY	∠
POSITION	⊕
CONCENTRICITY	◎
SYMMETRY	≡
CIRCULAR RUNOUT	↻

EMO SW
 【A165E-LS-24D-02】
 SIZE φ30
 (1)SW RATING
 AC125V 5A
 AC250V 3A
 DC30V 3A
 (2)LED RATING
 AC/DC24V 8mA
 COLOR RED


SW BOX



CABLE
 【 VCTF 0.5SQ-12C 】
 300VAC or less
 Finished outer diameter 9.6mm
 VCTF 0.5SQ-12C

REVISION				
MARK	DESCRIPTION	DATE	REVISED	APPROVED

SW LAYOUT



CABLE LENGTH : 1m

COMMON TOLERANCE	
OVER 0.5 UP TO 6mm	±0.1
OVER 6 UP TO 30mm	±0.2
OVER 30 UP TO 120mm	±0.3
OVER 120 UP TO 400mm	±0.5
TOLERANCE OF ANGLE	±0.5

(白)
(赤)
(緑)
(黄)
(茶)
(灰)

(注記)
 未使用の電線は端末を絶縁処理する事。

MATERIAL	HARDNESS	HEAT TREATMENT	SURFACE TREATMENT
3RD ANGLE PROJECTION	APPROVED		TITLE スイッチボックス(1個仕様) 型式: SAAF-1R-B
	CHECKED		
SCALE 1:1	DRAWN		
	NAME	DATE	DWG.No. SAAF-1R-B-0
MISUMI Corporation			