


TOLERANCING SYMBOL	JIS B 0021
STRAIGHTNESS	—
FLATNESS	▭
CIRCULARITY	○
CYLINDRICITY	⊗
LINE PROFILE	⤴
SURFACE PROFILE	⤴
PARALLELISM	∥
PERPENDICULARITY	⊥
ANGULARITY	∠
POSITION	⊕
CONCENTRICITY	⊙
SYMMETRY	≡
CIRCULAR RUNOUT	↻

EMO SW  
 【A165E-M-01】  
 SIZE φ40  
 (1)SW RATING  
 AC125V 5A  
 AC250V 3A  
 DC30V 3A  
 COLOR RED


SW BOX



CABLE  
 【 VCTF 0.5SQ-12C 】  
 300VAC or less  
 Finished outer diameter 9.6mm  
 VCTF 0.5SQ-12C

REVISION				
MARK	DESCRIPTION	DATE	REVISED	APPROVED

SW LAYOUT



CABLE LENGTH : 1m

- (黒)
- (白)
- (赤)
- (緑)
- (黄)
- (茶)
- (青)
- (灰)
- (空)
- (若葉)

(注記)  
 未使用の電線は末端を絶縁処理する事。

COMMON TOLERANCE	
OVER 0.5 UP TO 6mm	±0.1
OVER 6 UP TO 30mm	±0.2
OVER 30 UP TO 120mm	±0.3
OVER 120 UP TO 400mm	±0.5
TOLERANCE OF ANGLE	±0.5

MATERIAL	HARDNESS	HEAT TREATMENT	SURFACE TREATMENT
3RD ANGLE PROJECTION	APPROVED		TITLE スイッチボックス(1個仕様) 型式: SAAF-1R-C
	CHECKED		
SCALE 1:1	DRAWN		
	NAME	DATE	
MISUMI Corporation			DWG.No. SAAF-1R-C-0