


TOLERANCING SYMBOL	JIS B 0021
STRAIGHTNESS	—
FLATNESS	▭
CIRCULARITY	○
CYLINDRICITY	⊗
LINE PROFILE	⤴
SURFACE PROFILE	⤵
PARALLELISM	∥
PERPENDICULARITY	⊥
ANGULARITY	∠
POSITION	⊕
CONCENTRICITY	⊙
SYMMETRY	≡
CIRCULAR RUNOUT	↻

SW1
 【ARI16F0N-C1E3G】
 (1)SW RATING (抵抗負荷時)
 AC120V 1.5A
 AC240V 1A
 DC24V 1A
 (2)LED RATING
 AC/DC24V 7.5mA
 COLOR GREEN


EMO SW
 【ARI16VOL-02E3R】
 SIZE φ32
 (1)SW RATING (抵抗負荷時)
 AC120V 1.5A
 AC240V 1A
 DC24V 1A
 (2)LED RATING
 AC/DC24V 7.5mA
 COLOR RED

CABLE
 【VCTF 0.5SQ-12C】
 300VAC or less
 Finished outer diameter 9.6mm
 VCTF 0.5SQ-12C



(注記)
 未使用の電線は端末を絶縁処理する事。

REVISION				
MARK	DESCRIPTION	DATE	REVISED	APPROVED



CABLE LENGTH : 1m

COMMON TOLERANCE	
OVER 0.5 UP TO 6mm	±0.1
OVER 6 UP TO 30mm	±0.2
OVER 30 UP TO 120mm	±0.3
OVER 120 UP TO 400mm	±0.5
TOLERANCE OF ANGLE	±0.5

MATERIAL		HARDNESS		HEAT TREATMENT		SURFACE TREATMENT	
3RD ANGLE PROJECTION	APPROVED			TITLE			
	CHECKED			スイッチボックス(2個仕様)			
SCALE	DRAWN			型式: SAAF-2F-B			
1:1		NAME	DATE				
MISUMI Corporation				DWG.No. SAAF-2F-B-0			