


TOLERANCING SYMBOL JIS B 0021
STRAIGHTNESS
FLATNESS
CIRCULARITY
CYLINDRICITY
LINE PROFILE
SURFACE PROFILE
PARALLELISM
PERPENDICULARITY
ANGULARITY
POSITION
CONCENTRICITY
SYMMETRY
CIRCULAR RUNOUT


**SW1**  
 【A16L-JGM-24D-1】  
 (1)SW RATING  
 AC125V 5A  
 AC250V 3A  
 DC30V 3A  
 (2)LED RATING  
 AC/DC24V 8mA  
 COLOR GREEN

**EMO SW**  
 【A165E-LS-24D-02】  
 SIZE φ30  
 (1)SW RATING  
 AC125V 5A  
 AC250V 3A  
 DC30V 3A  
 (2)LED RATING  
 AC/DC24V 8mA  
 COLOR RED

**CABLE**  
 【 VCTF 0.5SQ-12C 】  
 300VAC or less  
 Finished outer diameter 9.6mm  
 VCTF 0.5SQ-12C



REVISION				
MARK	DESCRIPTION	DATE	REVISED	APPROVED



CABLE LENGTH : 1m

COMMON TOLERANCE	
OVER 0.5 UP TO 6mm	±0.1
OVER 6 UP TO 30mm	±0.2
OVER 30 UP TO 120mm	±0.3
OVER 120 UP TO 400mm	±0.5
TOLERANCE OF ANGLE	±0.5

(注記)  
 未使用の電線は末端を絶縁処理する事。

MATERIAL		HARDNESS		HEAT TREATMENT		SURFACE TREATMENT	
3RD ANGLE PROJECTION	APPROVED			TITLE スイッチボックス(2個仕様) 型式: SAAF-2R-B			
	CHECKED						
	DRAWN						
SCALE 1:1		NAME	DATE	DWG.No. SAAF-2R-B-0			
MISUMI Corporation							