


TOLERANCING SYMBOL	JIS B 0021
STRAIGHTNESS	—
FLATNESS	□
CIRCULARITY	○
CYLINDRICITY	⊗
LINE PROFILE	⤴
SURFACE PROFILE	⤴
PARALLELISM	∥
PERPENDICULARITY	⊥
ANGULARITY	∠
POSITION	⊕
CONCENTRICITY	⊙
SYMMETRY	≡
CIRCULAR RUNOUT	↻

SW1
 【A16-JGM-1】
 (1)SW RATING
 AC125V 5A
 AC250V 3A
 DC30V 3A
 COLOR GREEN


SW2
 【A16-JRM-1】
 (1)SW RATING
 AC125V 5A
 AC250V 3A
 DC30V 3A
 COLOR RED

EMO SW
 【A165E-LS-24D-02】
 SIZE φ30
 (1)SW RATING
 AC125V 5A
 AC250V 3A
 DC30V 3A
 (2)LED RATING
 AC/DC24V 8mA
 COLOR RED



(注記)
 未使用の電線は端末を絶縁処理する事。

REVISION				
MARK	DESCRIPTION	DATE	REVISED	APPROVED



CABLE LENGTH : 1m

COMMON TOLERANCE	
OVER 0.5 UP TO 6mm	±0.1
OVER 6 UP TO 30mm	±0.2
OVER 30 UP TO 120mm	±0.3
OVER 120 UP TO 400mm	±0.5
TOLERANCE OF ANGLE	±0.5

MATERIAL		HARDNESS		HEAT TREATMENT		SURFACE TREATMENT	
3RD ANGLE PROJECTION	APPROVED				TITLE		
	CHECKED				スイッチボックス(3個仕様)		
SCALE	DRAWN				型式: SAAF-3R-C		
1:1		NAME	DATE				
MISUMI Corporation					DWG.No. SAAF-3R-C-0		