


コネクタ変換・分岐ケーブル

三菱電機・オムロン対応ケーブル 結線図 商品ページ 591, 592

GRNT22 (GRPT22)




■結線図

CN1 FCN-367J040-AU-F CN3 B HIF3BA-20D-2.54R (MILE-20-2.54-S)

B20	20
B19	18
B18	16
1	1
B13	6
B12	4
B11	2
B10	19
B9	17
B8	15
1	1
B3	5
B2	3
B1	1
CN2 A HIF3BA-20D-2.54R (MILE-20-2.54-S)	
A20	20
A19	18
A18	16
1	1
A13	6
A12	4
A11	2
A10	19
A9	17
A8	15
1	1
A3	5
A2	3
A1	1

GRNT23 (GRPT23)




■結線図

CN1 FCN-367J040-AU-F CN2 mch HIF3BA-20D-2.54R (MILE-20-2.54-S)

A1	20
A2	18
A3	16
1	1
A8	6
A9	4
A10	2
A11	19
A12	17
A13	15
1	1
A18	5
A19	3
A20	1
CN3 m+1ch HIF3BA-20D-2.54R (MILE-20-2.54-S)	
B1	20
B2	18
B3	16
1	1
B8	6
B9	4
B10	2
B11	19
B12	17
B13	15
1	1
B18	5
B19	3
B20	1

GRNT24 (GRPT24)




■結線図

CN1 FCN-367J040-AU-F CN3 mch HIF3BA-20D-2.54R (MILE-20-2.54-S)

A1	20
A2	18
A3	16
1	1
A7	8
A8	6
A9	4
A10	19
A11	17
A12	15
1	1
A16	7
A17	5
A18	3
A19	2
A20	1
CN2 m+1ch HIF3BA-20D-2.54R (MILE-20-2.54-S)	
B1	20
B2	18
B3	16
1	1
B7	8
B8	6
B9	4
B10	19
B11	17
B12	15
1	1
B16	7
B17	5
B18	3
B19	2
B20	1

GRNT25 (GRPT25)




■結線図

CN1 FCN-367J040-AU-F CN3 HIF3BA-20D-2.54R (MILE-20-2.54-S)

A1	1
A2	2
A3	3
A4	4
A5	5
A6	7
A7	9
A8	11
A9	13
A10	15
A11	17
A12	19
A13	6
A14	8
A15	10
A16	12
A17	14
A18	16
A19	18
A20	20
CN2 HIF3BA-20D-2.54R (MILE-20-2.54-S)	
B1	1
B2	2
B3	3
B4	4
B5	5
B6	7
B7	9
B8	11
B9	13
B10	15
B11	17
B12	19
B13	6
B14	8
B15	10
B16	12
B17	14
B18	16
B19	18
B20	20

GRNT26 (GRPT26)




■結線図

CN1 FCN-367J040-AU-F CN3 HIF3BA-20D-2.54R (MILE-20-2.54-S)

A1	1
A2	2
A3	3
A4	4
A5	5
A6	7
A7	9
A8	11
A9	13
A10	15
A11	17
A12	19
A13	6
A14	8
A15	10
A16	12
A17	14
A18	16
A19	18
A20	20
CN2 HIF3BA-20D-2.54R (MILE-20-2.54-S)	
B1	1
B2	2
B3	3
B4	4
B5	5
B6	7
B7	9
B8	11
B9	13
B10	15
B11	17
B12	19
B13	6
B14	8
B15	10
B16	12
B17	14
B18	16
B19	18
B20	20

GRNT27 (GRPT27)




■結線図

CN1 FCN-367J040-AU-F CN B HIF3BA-20D-2.54R (MILE-20-2.54-S)

A1	2
A2	4
A3	1
A4	3
A5	5
A6	7
A7	9
A8	11
A9	13
A10	15
A11	17
A12	19
A13	6
A14	8
A15	10
A16	12
A17	14
A18	16
A19	18
A20	20
CN A HIF3BA-20D-2.54R (MILE-20-2.54-S)	
B1	2
B2	4
B3	1
B4	3
B5	5
B6	7
B7	9
B8	11
B9	13
B10	15
B11	17
B12	19
B13	6
B14	8
B15	10
B16	12
B17	14
B18	16
B19	18
B20	20

GRNT28 (GRPT28)



■結線図

CN1 FCN-367J024-AU-F CN2 HIF3BA-20D-2.54R (MILE-20-2.54-S)

A1	1
A2	3
A3	5
1	1
A8	15
A9	17
A10	19
A11	NC
A12	NC
B1	2
B2	4
B3	6
1	1
B8	18
B9	20
B10	NC
B11	NC
B12	NC

- コネクタ付ケーブル選定方法
- 角型コネクタ付ケーブル
- 同軸コネクタ付ケーブル
- 丸型コネクタ付ケーブル
- ナイロンコネクタ付ケーブル
- カスタムサービス

コネクタ付ケーブル資料