











































Han防水コネクタケーブル

▼ HANシリーズ 商品ページ 817

全芯数共通

CN1	線芯識別								CN2	
	Aケーブル		Bケーブル				Cケーブル			
ピンNo.は 118 ページ	例)10芯 ピンNo.8 		例)ピンNo.5 				例)10芯 ピンNo.8 		ピンNo.は 118 ページ	
芯数	絶縁体色	識別ライン色	対No.	線芯No.	絶縁体色	埋込ライン色	識別パターン	~12芯	16芯以上	芯数
1	黒		1	1	黒	—		黒	1	1
2	白		1	2	黒	白		白	2	2
3	赤		2	3	赤	—		赤	3	3
4	緑		2	4	赤	白		緑	4	4
5	黄		3	5	緑	—		黄	5	5
6	茶		3	6	緑	白		茶	6	6
7	青		4	7	黄	—		青	7	7
8	灰		4	8	黄	白		灰	8	8
9	橙		5	9	茶	—		橙	9	9
10	空		5	10	茶	白		紫	10	10
11	桃		6	11	青	—		桃	11	11
12	若葉		6	12	青	白		若草	12	12
13	紫		7	13	灰	—			13	13
14	白	黒	7	14	灰	白			14	14
15	白	赤	8	15	橙	—			15	15
16	白	緑	8	16	橙	白			16	16
17	白	黄	9	17	紫	—			17	17
18	白	茶	9	18	紫	白			18	18
19	白	青	10	19	若葉	—			19	19
20	白	橙	10	20	若葉	白			20	20
21	灰	黒	11	21	桃	—			21	21
22	灰	白	11	22	桃	白			22	22
23	灰	赤	12	23	空	—			23	23
24	灰	緑	12	24	空	白			24	24
25			13	25	白	—			25	25
26			13	26	白	黒			26	26
27			14	27	緑	黒			27	27
28			14	28	緑	赤			28	28
29			15	29	黄	黒			29	29
30			15	30	黄	赤			30	30
31			16	31	茶	黒			31	31
32			16	32	茶	赤			32	32
33			17	33	青	黒			33	33
34			17	34	青	赤			34	34
35			18	35	灰	黒			35	35
36			18	36	灰	赤			36	36
37			19	37	橙	黒			37	37
38			19	38	橙	赤			38	38
39			20	39	紫	黒			39	39
40			20	40	紫	赤			40	40
41			21	41	若葉	黒			41	41
42			21	42	若葉	赤			42	42

- コネクタ付ケーブル選定方法
- 角型コネクタ付ケーブル
- 同軸コネクタ付ケーブル
- 丸型コネクタ付ケーブル
- ナイロンコネクタ付ケーブル
- カスタムサービス
- コネクタ付ケーブル資料