


FLAT BARS
フラットバー
—ミガキ平鋼—



材料屋24でミスミ型番・出荷日・価格を一発表示!



種類	型式	材質
平鋼	FSS	SS400D
	FSC	S45CD
	FSSS	SUS304D
	FSSA	A6063S

Price 価格 WOSにてご確認ください。

■ FSS (材質SS400D) 価格

A 1mm単位	B	T	5	6	9	10	12	16	19	22	25	30	
30~50	16	16											
51~150													
151~300													
301~800													
30~50	22	22											
51~150													
151~300													
301~800													
30~50	25	25											
51~150													
151~300													
301~800													
30~50	32	32											
51~150													
151~300													
301~800													
30~50	38	38											
51~150													
151~300													
301~800													
30~50	50	50											
51~150													
151~300													
301~800													
30~50	60	60											
51~150													
151~300													
301~800													
30~50	75	75											
51~150													
151~300													
301~800													
30~50	100	100											
51~150													
151~300													
301~800													
30~50	125	125											
51~150													
151~300													
301~800													

Web 金額はWOSにてご確認ください。

■ FSC (材質S45CD) 価格

A 1mm単位	B	T	5	6	9	12	16	19	22	25	30		
30~50	16	16											
51~150													
151~300													
301~800													
30~50	22	22											
51~150													
151~300													
301~800													
30~50	25	25											
51~150													
151~300													
301~800													
30~50	32	32											
51~150													
151~300													
301~800													
30~50	38	38											
51~150													
151~300													
301~800													
30~50	50	50											
51~150													
151~300													
301~800													
30~50	60	60											
51~150													
151~300													
301~800													
30~50	75	75											
51~150													
151~300													
301~800													
30~50	100	100											
51~150													
151~300													
301~800													
30~50	125	125											
51~150													
151~300													
301~800													

Web 金額はWOSにてご確認ください。

■ FSSS (材質SUS304D) 価格

A 1mm単位	B	T	5	6	9	10	12	16	19	22	25	30	
30~50	15	15											
51~150													
151~300													
301~800													
30~50	20	20											
51~150													
151~300													
301~800													
30~50	25	25											
51~150													
151~300													
301~800													
30~50	32	32											
51~150													
151~300													
301~800													
30~50	38	38											
51~150													
151~300													
301~800													
30~50	50	50											
51~150													
151~300													
301~800													
30~50	65	65											
51~150													
151~300													
301~800													
30~50	100	100											
51~150													
151~300													
301~800													
30~50	125	125											
51~150													
151~300													
301~800													

Web 金額はWOSにてご確認ください。

■ FSSA (材質A6063S) 価格

A 1mm単位	B	T	5	6	8	10	12	15	20	25	30		
30~50	15	15											
51~150													
151~300													
301~800													
30~50	20	20											
51~150													
151~300													
301~800													
30~50	30	30											
51~150													
151~300													
301~800													
30~50	40	40											
51~150													
151~300													
301~800													
30~50	50	50											
51~150													
151~300													
301~800													
30~50	60	60											
51~150													
151~300													
301~800													
30~50	100	100											
51~150													
151~300													
301~800													

Web 金額はWOSにてご確認ください。

Order 注文例 型式 - A - B - T FSC - 560 - 25 - 9

Delivery 出荷日 2 日日出荷

ご注文締切
 ストックA早割 翌日出荷 300円/1明細行 PM 3:00迄
 ストックA 翌日出荷 800円/1本 PM 6:00迄 P134
 ●ストックA早割は1明細行当たり一律300円
 ●ストックAは3本以上で1明細行当たり一律2,160円
 ●21個以上は納期が変わる可能性があります。

■ 精度基準

項目	FSS・FSC	FSSS	FSSA
•T寸公差	5.6 9.10 12.16 19.30 0 0 0 0 -0.18 -0.22 -0.27 -0.3	5.6 9.10 12.16 19.30 0 0 0 0 -0.3 -0.22 -0.27 -0.33	5.6 8.12 15 20.25 30 ±0.27 ±0.3 ±0.35 ±0.38 ±0.45
•A寸公差	±0.15	±0.15	±0.15
•B寸公差	16 ~25 ~50 ~60 ~100 ~125 0 0 0 0 0 0 -0.18 -0.21 -0.25 -0.3 -0.35 -0.4	15 ~25 ~50 ~125 0 0 0 0 -0.27 -0.33 -0.39 -0.73	15 ~20 ~30 ~50 ~100 ±0.35 ±0.38 ±0.45 ±0.54 ±0.92
•曲り	100mmに対し0.1以下	100mmに対し0.1以下	100mmに対し0.1以下
•切断面取	C0.1~0.3	C0.1~0.3	C0.1~0.3

Alterations	Code	Spec.	¥/1Code
コーナーカット	CCA CCB CCD CCC	任意のコーナーをカットすることができます。 1≦コーナーカット≦10 1mm単位指定 指定方法 (例)AとDのコーナーを C5でカットする場合 → CCA5-CCD5	500/ 1コーナー