

HEXAGON SOCKET HEAD CAP SCREWS

六角穴付ボルト

—三価クロメート—

CADデータフォルダ名: 34_Screws

CBE

材質 SCM435
表面処理 三価クロメート
硬度 HRC32~39
※強度区分 10.9

RoHS10

M×P	A	E	B
2×0.4	3.8	2	1.5
2.6×0.45	4.5	2.6	2
3×0.5	5.5	3	2.5
4×0.7	7	4	3
5×0.8	8.5	5	4
6×1.0	10	6	5
8×1.25	13	8	6
10×1.5	16	10	8
12×1.75	18	12	10

※強度区分とは、ネジの引張強さです。

(例) 10.9
降伏点または耐力の最小値が引張強さの90%であることを示します。
引張強さの最小値が1040N/mm²であることを示します。

参考: 六角穴付ボルトに対するザグリ及びボルトの寸法 P.1945

型式	ℓ	¥基準単価				¥スライド単価			
		Type M-L	1~9本	10~19本	20~49本	50~500本			
CBE 2-5	5	120	72	48	30				
6	6	120	72	48	30				
8	8	120	72	48	30				
10	10	120	72	48	30				
CBE 2.6-5	5	110	61	44	30				
6	6	110	61	44	30				
8	8	120	66	48	30				
10	10	120	66	48	30				
CBE 3-4	4	79	55	32	25				
5	5	69	31	28	22				
6	6	69	31	28	19				
8	8	69	31	28	19				
10	10	74	33	30	22				
12	12	74	33	30	22				
15	15	74	33	30	22				
18	18	74	33	30	22				
20	20	74	33	30	22				
25	25	77	35	31	24				
30	30	82	37	33	28				
35	35	82	45	33	28				
CBE 4-5	5	84	46	34	25				
6	6	74	33	30	22				
8	8	74	33	30	22				
10	10	74	33	30	22				
12	12	79	36	32	22				
15	15	79	36	32	24				
18	18	79	36	32	24				
20	20	79	36	32	24				
25	25	79	36	32	24				
30	30	84	38	34	31				
35	35	87	39	35	33				
40	40	94	42	40	39				
45	45	94	42	40	39				
50	50	94	42	40	39				
CBE 5-6	6	94	42	38	25				
8	8	74	33	30	22				
10	10	74	33	30	22				
12	12	74	33	30	22				

型式	ℓ	¥基準単価				¥スライド単価			
		Type M-L	1~9本	10~19本	20~49本	50~500本			
CBE 5-15	15	74	33	30	24				
18	18	79	36	32	28				
20	20	79	36	32	28				
25	25	79	36	32	28				
30	30	87	39	35	33				
35	35	94	42	41	39				
40	40	99	45	44	43				
45	45	100	49	48	47				
50	50	105	53	52	51				
CBE 6-8	8	89	40	36	24				
10	10	74	33	30	24				
12	12	74	33	30	24				
15	15	74	33	30	24				
18	18	79	36	32	28				
20	20	79	36	32	28				
25	25	79	36	32	28				
30	30	87	39	35	33				
35	35	94	42	41	39				
40	40	99	45	44	43				
45	45	105	52	51	50				
50	50	110	56	55	54				
55	55	110	56	55	54				
60	60	145	65	58	54				
65	65	155	70	62	54				
70	70	165	74	66	60				
75	75	200	90	80	70				
CBE 8-10	10	110	54	53	52				
12	12	94	42	41	39				
15	15	94	42	41	39				
18	18	94	42	41	39				
20	20	94	42	41	39				
25	25	99	45	44	43				
30	30	99	45	44	43				
35	35	110	57	56	55				
40	40	115	63	62	61				
45	45	115	67	66	65				
50	50	125	89	88	87				
55	55	125	110	109	108				

型式	ℓ	¥基準単価				¥スライド単価			
		Type M-L	1~9本	10~19本	20~49本	50~500本			
CBE 8-60	60	135	132	131	130				
65	65	155	142	141	140				
70	70	175	150	145	140				
75	75	200	160	150	140				
80	80	250	180	160	140				
CBE 10-15	15	120	68	66	65				
20	20	120	68	66	65				
25	25	120	68	66	65				
30	30	130	75	70	69				
35	35	140	84	75	72				
40	40	150	90	80	74				
45	45	160	96	85	80				
50	50	190	114	90	80				
55	55	190	114	90	87				
60	60	200	120	95	87				
65	65	200	120	110	100				
70	70	200	120	110	100				
75	75	200	120	110	100				
CBE 12-15	15	170	119	90	75				
20	20	170	119	90	75				
25	25	170	119	90	77				
30	30	190	133	100	80				
35	35	210	147	110	85				
40	40	240	168	120	89				
45	45	260	182	125	92				
50	50	280	196	130	98				
55	55	300	210	140	100				
60	60	330	231	150	108				

Order 注文例

型式 CBE4-10

Delivery 出荷日

在庫品 翌日出荷 P.133

ご希望によりPM6:00迄、当日出荷受付致します。

数量区分	標準対応	個別対応
数量	1~500	501~
出荷日	通常	お見積り

表示数量超えはWOSにてご確認ください。

HEXAGON SOCKET HEAD CAP SCREWS / HEXAGON SOCKET HEAD CAP SCREWS

六角穴付ボルト/六角穴付ボルト

—三価クロメート・パック販売— —ユニクロメッキ—

CADデータフォルダ名: 34_Screws

PACK-SCBE

材質 SCM435
表面処理 三価クロメート
硬度 HRC32~39
※強度区分 10.9

RoHS10

CBM

材質 SCM435
表面処理 ユニクロメッキ
硬度 HRC32~39
※強度区分 10.9

CBMはRoHS非対応

型式	ℓ	PACK-SCBE パック入数	PACK-SCBE	
			¥基準単価	¥スライド単価
Type M-L				
PACK-SCBE 2-5	5	1,500	900	
6	6			
8	8			
10	10			
PACK-SCBE 2.6-5	5	1,480	880	
6	6			
8	8			
10	10			
PACK-SCBE 3-5	5	1,100	680	
6	6	940	560	
8	8			
10	10			
12	12	1,100	680	
15	15			
20	20	1,190	710	
25	25	1,390	820	
30	30			
35	35			
PACK-SCBE 4-6	6	1,100	680	
8	8			
10	10			
12	12			
15	15			
20	20	1,190	710	
25	25	1,520	890	
30	30	1,610	960	
35	35	1,910	1,140	
40	40			
45	45			
PACK-SCBE 5-8	8	1,100	680	
10	10			
12	12			
15	15			
20	20	1,190	710	
25	25	1,370	820	
30	30	1,610	960	
35	35	1,910	1,140	
40	40	2,130	1,260	
45	45	2,350	1,390	
50	50	2,550	1,520	

型式	ℓ	PACK-SCBE パック入数	PACK-SCBE	
			¥基準単価	¥スライド単価
Type M-L				
PACK-SCBE 6-8	8	1,190	710	
10	10			
12	12			
15	15			
20	20	1,370	820	
25	25	1,610	960	
30	30	1,910	1,140	
35	35	2,130	1,260	
40	40	2,480	1,470	
45	45			
50	50	2,690	1,600	
60	60			
PACK-SCBE 8-12	12	1,950	1,180	
15	15			
20	20	2,150	1,300	
25	25	2,710	1,660	
30	30	3,020	1,830	
35	35	3,230	1,960	
40	40	4,330	2,610	
45	45	5,400	3,260	
50	50	6,500	3,910	
60	60			
PACK-SCBE 10-15	15	1,300	780	
20	20	1,380	820	
25	25	1,440	860	
30	30	1,480	880	
35	35	1,600	960	
40	40	1,740	1,000	
45	45	1,540	920	
50	50	1,600	960	
55	55	1,700	1,020	
60	60	1,780	1,060	
*50	*50	1,840	1,100	
55	55	1,950	1,170	
60	60	2,000	1,200	
60	60	2,160	1,300	

*ℓ部はJIS B 1176に基づきます。

Order 注文例

型式 PACK-SCBE6-10 CBM8-20

Delivery 出荷日

在庫品 翌日出荷 P.133

ご希望によりPM6:00迄、当日出荷受付致します。

PACK-SCBEはパック販売、CBMは単品販売となります。
パック販売品は注文数量1でパック納入されます。

型式	ℓ	¥基準単価	¥スライド単価	型式	ℓ	¥基準単価	¥スライド単価
Type M-L				Type M-L			
CBM 3-6	6	15	5	CBM 8-12	12	40	25
8	8			15	15	36	14
10	10			20	20	40	15
12	12			25	25	48	19
15	15			30	30	55	21
20	20	17	6	35	35	61	24
25	25			40	40	80	31
30	30			45	45	101	40
35	35			50	50	122	48
CBM 4-6	6	19	7	CBM 10-15	15	61	24
8	8			20	20	71	28
10	10			25	25	80	31
12	12			30	30	92	36
15	15			35	35	101	40
18	18			40	40	122	48
20	20			45	45	141	56
25	25			50	50	166	66
30	30			55	55		
35	35			60	60		
CBM 5-8	8	19	7	CBM 12-15	15	101	40
10	10			20	20	120	47
12	12			25	25	141	56
15	15			30	30	164	65
20	20			35	35	187	74
25	25			40	40	202	80
30	30			45	45	229	91
35	35			50	50	242	96
40	40			55	55		
45	45			60	60		
CBM 6-8	8	25	17				
10	10						
12	12						