

# URETHANES FOR HEAVY LOAD 高荷重用ウレタン

D	D <sub>T</sub>	d <sub>T</sub>	L <sub>T</sub>
15			
20			
25	±0.2	±0.2	±0.3
30			
40			
50	±0.3	±0.2	±0.5
60			
80	±0.4	±0.2	±0.5
100			

製品概要 P.1633 荷重グラフ P.1635 硬度 ショアA90

F=L×15%		F=L×20%		F=L×25%		d	型式 Type D - L
F mm	荷重 N(kgf)	F mm	荷重 N(kgf)	F mm	荷重 N(kgf)		
3.8		5.0		6.3			A 15 - 25
4.5	588	6.0	785	7.5	981	18	30
5.3	{60}	7.0	{80}	8.8	{100}		35
6.0		8.0		10.0			40
3.8		5.0		6.3			A 20 - 25
4.5	1128	6.0	1422	7.5	1765	24	30
5.3	{115}	7.0	{145}	8.8	{180}		35
6.0		8.0		10.0			40
3.8		5.0		6.3			A 25 - 25
4.5		6.0		7.5			30
5.3	1667	7.0	2157	8.8	2648	30	35
6.0	{170}	8.0	{220}	10.0	{270}		40
6.8		9.0		11.3			45
7.5		10.0		12.5			50
3.8		5.0		6.3			A 30 - 25
4.5		6.0		7.5			30
5.3		7.0		8.8			35
6.0	2599	8.0	3040	10.0	3531	37	40
6.8	{265}	9.0	{310}	11.3	{360}		45
7.5		10.0		12.5			50
8.3		11.0		13.8			55
9.0		12.0		15.0			60
6.0		8.0		10.0			A 40 - 40
7.5	4560	10.0	5394	12.5	6276	48	50
9.0	{465}	12.0	{550}	15.0	{640}		60
7.5		10.0		12.5			A 50 - 50
9.0	7747	12.0	9218	15.0	10787	60	60
12.0	{790}	16.0	{940}	20.0	{1100}		80
7.5		10.0		12.5			A 60 - 50
9.0	13042	12.0	15102	15.0	17652	72	60
12.0	{1330}	16.0	{1540}	20.0	{1800}		80
9.0		12.0		15.0			A 80 - 60
12.0	21378	16.0	25399	20.0	29420	95	80
15.0	{2180}	20.0	{2590}	25.0	{3000}		100
12.0		16.0		20.0			A 100 - 80
15.0	35990	20.0	42659	25.0	49720	119	100
18.0	{3670}	24.0	{4350}	30.0	{5070}		120

•荷重 [kgf] = 荷重N×0.101972

Order 注文例 型式 A 25-40

Delivery 出荷日 在庫品

Alterations 追加加工 型式 - (C1) A 60-80 - C1 3 日日出荷

追加加工	記号	詳細
	C1	内径にC1面取り加工

### 全長ロングタイプ

D	D <sub>T</sub>	d <sub>T</sub>	L <sub>T</sub>
8			
10			
15			
20	±0.2		
25			
30			
40			
50	±0.2		
60			
80	±0.3		
100	±0.4		

製品概要 P.1633 硬度 ショアA90

d	型式		型式	
	Type	D-L	Type	D-L
-	-	-	C	8-200
-	-	-	C	10-200
7	LA	15-200	C	15-200
8.5	LA	20-200	C	20-200
11	LA	25-200	C	25-200
14	LA	30-500	C	30-500
	LA	40-500	C	40-500
	LA	50-500	C	50-500
	LA	60-500	C	60-500
22	LA	80-500	C	80-500
	LA	100-500	C	100-500

Order 注文例 型式 LA 60-500

Delivery 出荷日 在庫品

### 全長指定タイプ

D	D <sub>T</sub>	d <sub>T</sub>	L <sub>T</sub>
8			
10			
15			
20	±0.2		±0.3
25			
30			
40			
50	±0.2		
60	±0.3		±0.5
80	±0.4		
100			

製品概要 P.1633 硬度 ショアA90

d	型式	D	L 指定1mm単位
-		10	
7		15	
8.5		20	
11		25	
14	AX	30	10 ~ 200
		40	
		50	
		60	
22	CX	80	
		100	

Order 注文例 型式 AX D - L 20 - 45

Delivery 出荷日 3 日日出荷

ストーク T  
ストーク A

ご注文の品名