



ECONOMY URETHANES エコノミーウレタン



AE



N (kgf)
V
F
L
D
d

D	D _T	d _T	L _T
15			
20			
25	±0.2		±0.3
30		±0.2	
40			
50	±0.3		±0.5
60			

製品概要 P.1633 荷重グラフ P.1635 硬度 ショアA90


F=L×15%		F=L×20%		F=L×25%			d	型式 Type D - L
F mm	荷重 N(kgf)	F mm	荷重 N(kgf)	F mm	荷重 N(kgf)	V		
3.8		5.0		6.3				AE 15 - 25
4.5	539	6.0	735	7.5	932	18	7	30
5.3	{55}	7.0	{75}	8.8	{95}			35
6.0		8.0		10.0				40
3.8		5.0		6.3				AE 20 - 25
4.5	1079	6.0	1373	7.5	1667	24	8.5	30
5.3	{110}	7.0	{140}	8.8	{170}			35
6.0		8.0		10.0				40
3.8		5.0		6.3				AE 25 - 25
4.5	1569	6.0	2059	7.5	2550	30	11	30
5.3	{160}	7.0	{210}	8.8	{260}			35
6.0		8.0		10.0				40
6.8		9.0		11.3				45
7.5		10.0		12.5				50
4.5		6.0		7.5				AE 30 - 30
5.3	2452	7.0	2844	8.8	3334	37	14	35
6.0	{250}	8.0	{290}	10.0	{340}			40
6.8		9.0		11.3				45
7.5		10.0		12.5				50
8.3		11.0		13.8				55
9.0		12.0		15.0				60
6.0	4315	8.0	5099	10.0	5982	48	14	AE 40 - 40
7.5	{440}	10.0	{520}	12.5	{610}			50
9.0		12.0		15.0				60
7.5	7355	10.0	8728	12.5	10297	60	14	AE 50 - 50
9.0	{750}	12.0	{890}	15.0	{1050}			60
12.0		16.0		20.0				80
7.5	12356	10.0	14318	12.5	16769	72	14	AE 60 - 50
9.0	{1260}	12.0	{1460}	15.0	{1710}			60
12.0		16.0		20.0				80

•荷重 [kgf] = 荷重N × 0.101972

Order 注文例 **型式** AE 15-25


Delivery 出荷日 **3** 日目出荷 **ストーク T** **ストーク A**

ex Example 使用例




下死点ですプリングガイド(SGA)の上部に、X≧10mm となるように安全を見込んで、Lを選択してください。


全長ロングタイプ



LAE



CE



D	D _T	d _T	L _T
8			
10			
15	±0.2		±0.2
20		±0.2	
25			
30			
40	±0.3		±0.5
50			
60			

製品概要 P.1633 硬度 ショアA90


d	型式		型式	
	Type	D-L	Type	D-L
-	-	-	CE	8-200
-	-	-	CE	10-200
7	LAE	15-200	CE	15-200
8.5	LAE	20-200	CE	20-200
11	LAE	25-200	CE	25-200
14	LAE	30-500	CE	30-500
	LAE	40-500	CE	40-500
	LAE	50-500	CE	50-500
			CE	60-500

Order 注文例 **型式** LAE 30-500


Delivery 出荷日 **3** 日目出荷

ストーク T **ストーク A**


全長指定タイプ



AEX



CEX



D	D _T	d _T	L _T
8			
10			
15	±0.2		±0.3
20		±0.2	
25			
30			
40			
50	±0.3		±0.5
60			

製品概要 P.1633 硬度 ショアA90

d	型式	D	L	
			指定1mm単位	
-	CEX	8	10 ~ 200	
-		10		
7		15		
8.5	20			
11	25			
14	30			
	AEX	40		
		50		
		60		

Order 注文例 **型式** AEX **D** 20 **L** 52

Delivery 出荷日 **3** 日目出荷

ストーク T **ストーク A**