

HR25コネクタ付ケーブル(Cable with HR25connector) 部材表

ハーネス型番	使用部材				芯数	
	CN1		CN2			ケーブル
	コネクタ	個数	コネクタ	個数		
HR25J-JP-A-4	HR25-7TJ-4P(72)	1			NA28WSH-3P-100	4
HR25J-JP-A-6	HR25-7TJ-6P(72)	1			NA28WSH-3P-100	6
HR25J-JP-A-8	HR25-7TJ-8P(72)	1			NA28WSH-6P-100	8
HR25J-JP-A-12	HR25-9TJ-12P(72)	1			NA28WSH-6P-100	12
HR25J-JP-A-16	HR25-9TJ-16P(72)	1			NA28WSH-10P-100	16
HR25J-JP-A-20	HR25-9TJ-20P(72)	1			NA28WSH-10P-100	20
HR25J-JS-A-4	HR25-7TJ-4S(72)	1			NA28WSH-3P-100	4
HR25J-JS-A-6	HR25-7TJ-6S(72)	1			NA28WSH-3P-100	6
HR25J-JS-A-8	HR25-7TJ-8S(72)	1			NA28WSH-6P-100	8
HR25J-JS-A-12	HR25-9TJ-12S(72)	1			NA28WSH-6P-100	12
HR25J-JS-A-16	HR25-9TJ-16S(72)	1			NA28WSH-10P-100	16
HR25J-JS-A-20	HR25-9TJ-20S(73)	1			NA28WSH-10P-100	20
HR25J-JPP-A-4	HR25-7TJ-4P(72)	1	HR25-7TP-4P(72)	1	NA28WSH-3P-100	4
HR25J-JPP-A-6	HR25-7TJ-6P(72)	1	HR25-7TP-6P(72)	1	NA28WSH-3P-100	6
HR25J-JPP-A-8	HR25-7TJ-8P(72)	1	HR25-7TP-8P(72)	1	NA28WSH-6P-100	8
HR25J-JPP-A-12	HR25-9TJ-12P(72)	1	HR25-9TP-12P(72)	1	NA28WSH-6P-100	12
HR25J-JPP-A-16	HR25-9TJ-16P(72)	1	HR25-9TP-16P(74)	1	NA28WSH-10P-100	16
HR25J-JPP-A-20	HR25-9TJ-20P(72)	1	HR25-9TP-20P(72)	1	NA28WSH-10P-100	20
HR25J-JSS-A-4	HR25-7TJ-4S(72)	1	HR25-7TP-4S(72)	1	NA28WSH-3P-100	4
HR25J-JSS-A-6	HR25-7TJ-6S(72)	1	HR25-7TP-6S(72)	1	NA28WSH-3P-100	6
HR25J-JSS-A-8	HR25-7TJ-8S(72)	1	HR25-7TP-8S(72)	1	NA28WSH-6P-100	8
HR25J-JSS-A-12	HR25-9TJ-12S(72)	1	HR25-9TP-12S(72)	1	NA28WSH-6P-100	12
HR25J-JSS-A-16	HR25-9TJ-16S(72)	1	HR25-9TP-16S(73)	1	NA28WSH-10P-100	16
HR25J-JSS-A-20	HR25-9TJ-20S(73)	1	HR25-9TP-20S(73)	1	NA28WSH-10P-100	20
HR25J-JPS-A-4	HR25-7TJ-4P(72)	1	HR25-7TP-4S(72)	1	NA28WSH-3P-100	4
HR25J-JPS-A-6	HR25-7TJ-6P(72)	1	HR25-7TP-6S(72)	1	NA28WSH-3P-100	6
HR25J-JPS-A-8	HR25-7TJ-8P(72)	1	HR25-7TP-8S(72)	1	NA28WSH-6P-100	8
HR25J-JPS-A-12	HR25-9TJ-12P(72)	1	HR25-9TP-12S(72)	1	NA28WSH-6P-100	12
HR25J-JPS-A-16	HR25-9TJ-16P(72)	1	HR25-9TP-16S(73)	1	NA28WSH-10P-100	16
HR25J-JPS-A-20	HR25-9TJ-20P(72)	1	HR25-9TP-20S(73)	1	NA28WSH-10P-100	20
HR25J-JSP-A-4	HR25-7TJ-4S(72)	1	HR25-7TP-4P(72)	1	NA28WSH-3P-100	4
HR25J-JSP-A-6	HR25-7TJ-6S(72)	1	HR25-7TP-6P(72)	1	NA28WSH-3P-100	6
HR25J-JSP-A-8	HR25-7TJ-8S(72)	1	HR25-7TP-8P(72)	1	NA28WSH-6P-100	8
HR25J-JSP-A-12	HR25-9TJ-12S(72)	1	HR25-9TP-12P(72)	1	NA28WSH-6P-100	12
HR25J-JSP-A-16	HR25-9TJ-16S(72)	1	HR25-9TP-16P(74)	1	NA28WSH-10P-100	16
HR25J-JSP-A-20	HR25-9TJ-20S(73)	1	HR25-9TP-20P(72)	1	NA28WSH-10P-100	20
HR25J-JPY-A-4	HR25-7TJ-4P(72)	1	F0.3-3.5	4	NA28WSH-3P-100	4
HR25J-JPY-A-6	HR25-7TJ-6P(72)	1	F0.3-3.5	6	NA28WSH-3P-100	6
HR25J-JPY-A-8	HR25-7TJ-8P(72)	1	F0.3-3.5	8	NA28WSH-6P-100	8
HR25J-JPY-A-12	HR25-9TJ-12P(72)	1	F0.3-3.5	12	NA28WSH-6P-100	12
HR25J-JPY-A-16	HR25-9TJ-16P(72)	1	F0.3-3.5	16	NA28WSH-10P-100	16
HR25J-JPY-A-20	HR25-9TJ-20P(72)	1	F0.3-3.5	20	NA28WSH-10P-100	20
HR25J-JSY-A-4	HR25-7TJ-4S(72)	1	F0.3-3.5	4	NA28WSH-3P-100	4
HR25J-JSY-A-6	HR25-7TJ-6S(72)	1	F0.3-3.5	6	NA28WSH-3P-100	6
HR25J-JSY-A-8	HR25-7TJ-8S(72)	1	F0.3-3.5	8	NA28WSH-6P-100	8
HR25J-JSY-A-12	HR25-9TJ-12S(72)	1	F0.3-3.5	12	NA28WSH-6P-100	12
HR25J-JSY-A-16	HR25-9TJ-16S(72)	1	F0.3-3.5	16	NA28WSH-10P-100	16
HR25J-JSY-A-20	HR25-9TJ-20S(73)	1	F0.3-3.5	20	NA28WSH-10P-100	20
HR25J-JPT-A-4	HR25-7TJ-4P(72)	1			NA28WSH-3P-100	4
HR25J-JPT-A-6	HR25-7TJ-6P(72)	1			NA28WSH-3P-100	6
HR25J-JPT-A-8	HR25-7TJ-8P(72)	1			NA28WSH-6P-100	8
HR25J-JPT-A-12	HR25-9TJ-12P(72)	1			NA28WSH-6P-100	12
HR25J-JPT-A-16	HR25-9TJ-16P(72)	1			NA28WSH-10P-100	16

HR25J-JPT-A-20	HR25-9TJ-20P(72)	1			NA28WSH-10P-100	20
HR25J-JST-A-4	HR25-7TJ-4S(72)	1			NA28WSH-3P-100	4
HR25J-JST-A-6	HR25-7TJ-6S(72)	1			NA28WSH-3P-100	6
HR25J-JST-A-8	HR25-7TJ-8S(72)	1			NA28WSH-6P-100	8
HR25J-JST-A-12	HR25-9TJ-12S(72)	1			NA28WSH-6P-100	12
HR25J-JST-A-16	HR25-9TJ-16S(72)	1			NA28WSH-10P-100	16
HR25J-JST-A-20	HR25-9TJ-20S(73)	1			NA28WSH-10P-100	20
HR25J-JPJP-A-4	HR25-7TJ-4P(72)	1	HR25-7TJ-4P(72)	1	NA28WSH-3P-100	4
HR25J-JPJP-A-6	HR25-7TJ-6P(72)	1	HR25-7TJ-6P(72)	1	NA28WSH-3P-100	6
HR25J-JPJP-A-8	HR25-7TJ-8P(72)	1	HR25-7TJ-8P(72)	1	NA28WSH-6P-100	8
HR25J-JPJP-A-12	HR25-9TJ-12P(72)	1	HR25-9TJ-12P(72)	1	NA28WSH-6P-100	12
HR25J-JPJP-A-16	HR25-9TJ-16P(72)	1	HR25-9TJ-16P(72)	1	NA28WSH-10P-100	16
HR25J-JPJP-A-20	HR25-9TJ-20P(72)	1	HR25-9TJ-20P(72)	1	NA28WSH-10P-100	20
HR25J-JSJS-A-4	HR25-7TJ-4S(72)	1	HR25-7TJ-4S(72)	1	NA28WSH-3P-100	4
HR25J-JSJS-A-6	HR25-7TJ-6S(72)	1	HR25-7TJ-6S(72)	1	NA28WSH-3P-100	6
HR25J-JSJS-A-8	HR25-7TJ-8S(72)	1	HR25-7TJ-8S(72)	1	NA28WSH-6P-100	8
HR25J-JSJS-A-12	HR25-9TJ-12S(72)	1	HR25-9TJ-12S(72)	1	NA28WSH-6P-100	12
HR25J-JSJS-A-16	HR25-9TJ-16S(72)	1	HR25-9TJ-16S(72)	1	NA28WSH-10P-100	16
HR25J-JSJS-A-20	HR25-9TJ-20S(73)	1	HR25-9TJ-20S(73)	1	NA28WSH-10P-100	20
HR25J-JPJS-A-4	HR25-7TJ-4P(72)	1	HR25-7TJ-4S(72)	1	NA28WSH-3P-100	4
HR25J-JPJS-A-6	HR25-7TJ-6P(72)	1	HR25-7TJ-6S(72)	1	NA28WSH-3P-100	6
HR25J-JPJS-A-8	HR25-7TJ-8P(72)	1	HR25-7TJ-8S(72)	1	NA28WSH-6P-100	8
HR25J-JPJS-A-12	HR25-9TJ-12P(72)	1	HR25-9TJ-12S(72)	1	NA28WSH-6P-100	12
HR25J-JPJS-A-16	HR25-9TJ-16P(72)	1	HR25-9TJ-16S(72)	1	NA28WSH-10P-100	16
HR25J-JPJS-A-20	HR25-9TJ-20P(72)	1	HR25-9TJ-20S(73)	1	NA28WSH-10P-100	20
HR25R-RPT-V-4	HR25-7TR-4P(73)	1			UL1007-28-BE-100	4
HR25R-RPT-V-6	HR25-7TR-6P(73)	1			UL1007-28-BE-100	6
HR25R-RPT-V-8	HR25-7TR-8P(73)	1			UL1007-28-BE-100	8
HR25R-RPT-V-12	HR25-9TR-12P(71)	1			UL1007-28-BE-100	12
HR25R-RPT-V-16	HR25-9TR-16P(71)	1			UL1007-28-BE-100	16
HR25R-RPT-V-20	HR25-9TR-20P(71)	1			UL1007-28-BE-100	20
HR25R-RST-V-4	HR25-7TR-4S(73)	1			UL1007-28-BE-100	4
HR25R-RST-V-6	HR25-7TR-6S(73)	1			UL1007-28-BE-100	6
HR25R-RST-V-8	HR25-7TR-8S(73)	1			UL1007-28-BE-100	8
HR25R-RST-V-12	HR25-9TR-12S(71)	1			UL1007-28-BE-100	12
HR25R-RST-V-16	HR25-9TR-16S(71)	1			UL1007-28-BE-100	16
HR25R-RST-V-20	HR25-9TR-20S(71)	1			UL1007-28-BE-100	20
HR25P-P-A-4	HR25-7TP-4P(72)	1			NA28WSH-3P-100	4
HR25P-P-A-6	HR25-7TP-6P(72)	1			NA28WSH-3P-100	6
HR25P-P-A-8	HR25-7TP-8P(72)	1			NA28WSH-6P-100	8
HR25P-P-A-12	HR25-9TP-12P(72)	1			NA28WSH-6P-100	12
HR25P-P-A-16	HR25-9TP-16P(74)	1			NA28WSH-10P-100	16
HR25P-P-A-20	HR25-9TP-20P(72)	1			NA28WSH-10P-100	20
HR25P-S-A-4	HR25-7TP-4S(72)	1			NA28WSH-3P-100	4
HR25P-S-A-6	HR25-7TP-6S(72)	1			NA28WSH-3P-100	6
HR25P-S-A-8	HR25-7TP-8S(72)	1			NA28WSH-6P-100	8
HR25P-S-A-12	HR25-9TP-12S(72)	1			NA28WSH-6P-100	12
HR25P-S-A-16	HR25-9TP-16S(73)	1			NA28WSH-10P-100	16
HR25P-S-A-20	HR25-9TP-20S(73)	1			NA28WSH-10P-100	20
HR25P-PP-A-4	HR25-7TP-4P(72)	1	HR25-7TP-4P(72)	1	NA28WSH-3P-100	4
HR25P-PP-A-6	HR25-7TP-6P(72)	1	HR25-7TP-6P(72)	1	NA28WSH-3P-100	6
HR25P-PP-A-8	HR25-7TP-8P(72)	1	HR25-7TP-8P(72)	1	NA28WSH-6P-100	8
HR25P-PP-A-12	HR25-9TP-12P(72)	1	HR25-9TP-12P(72)	1	NA28WSH-6P-100	12
HR25P-PP-A-16	HR25-9TP-16P(74)	1	HR25-9TP-16P(74)	1	NA28WSH-10P-100	16
HR25P-PP-A-20	HR25-9TP-20P(72)	1	HR25-9TP-20P(72)	1	NA28WSH-10P-100	20
HR25P-SS-A-4	HR25-7TP-4S(72)	1	HR25-7TP-4S(72)	1	NA28WSH-3P-100	4
HR25P-SS-A-6	HR25-7TP-6S(72)	1	HR25-7TP-6S(72)	1	NA28WSH-3P-100	6
HR25P-SS-A-8	HR25-7TP-8S(72)	1	HR25-7TP-8S(72)	1	NA28WSH-6P-100	8
HR25P-SS-A-12	HR25-9TP-12S(72)	1	HR25-9TP-12S(72)	1	NA28WSH-6P-100	12

HR25P-SS-A-16	HR25-9TP-16S(73)	1	HR25-9TP-16S(73)	1	NA28WSH-10P-100	16
HR25P-SS-A-20	HR25-9TP-20S(73)	1	HR25-9TP-20S(73)	1	NA28WSH-10P-100	20
HR25P-PS-A-4	HR25-7TP-4P(72)	1	HR25-7TP-4S(72)	1	NA28WSH-3P-100	4
HR25P-PS-A-6	HR25-7TP-6P(72)	1	HR25-7TP-6S(72)	1	NA28WSH-3P-100	6
HR25P-PS-A-8	HR25-7TP-8P(72)	1	HR25-7TP-8S(72)	1	NA28WSH-6P-100	8
HR25P-PS-A-12	HR25-9TP-12P(72)	1	HR25-9TP-12S(72)	1	NA28WSH-6P-100	12
HR25P-PS-A-16	HR25-9TP-16P(74)	1	HR25-9TP-16S(73)	1	NA28WSH-10P-100	16
HR25P-PS-A-20	HR25-9TP-20P(72)	1	HR25-9TP-20S(73)	1	NA28WSH-10P-100	20
HR25P-PY-A-4	HR25-7TP-4P(72)	1	F0.3-3.5	4	NA28WSH-3P-100	4
HR25P-PY-A-6	HR25-7TP-6P(72)	1	F0.3-3.5	6	NA28WSH-3P-100	6
HR25P-PY-A-8	HR25-7TP-8P(72)	1	F0.3-3.5	8	NA28WSH-6P-100	8
HR25P-PY-A-12	HR25-9TP-12P(72)	1	F0.3-3.5	12	NA28WSH-6P-100	12
HR25P-PY-A-16	HR25-9TP-16P(74)	1	F0.3-3.5	16	NA28WSH-10P-100	16
HR25P-PY-A-20	HR25-9TP-20P(72)	1	F0.3-3.5	20	NA28WSH-10P-100	20
HR25P-SY-A-4	HR25-7TP-4S(72)	1	F0.3-3.5	4	NA28WSH-3P-100	4
HR25P-SY-A-6	HR25-7TP-6S(72)	1	F0.3-3.5	6	NA28WSH-3P-100	6
HR25P-SY-A-8	HR25-7TP-8S(72)	1	F0.3-3.5	8	NA28WSH-6P-100	8
HR25P-SY-A-12	HR25-9TP-12S(72)	1	F0.3-3.5	12	NA28WSH-6P-100	12
HR25P-SY-A-16	HR25-9TP-16S(73)	1	F0.3-3.5	16	NA28WSH-10P-100	16
HR25P-SY-A-20	HR25-9TP-20S(73)	1	F0.3-3.5	20	NA28WSH-10P-100	20
HR25P-PT-A-4	HR25-7TP-4P(72)	1			NA28WSH-3P-100	4
HR25P-PT-A-6	HR25-7TP-6P(72)	1			NA28WSH-3P-100	6
HR25P-PT-A-8	HR25-7TP-8P(72)	1			NA28WSH-6P-100	8
HR25P-PT-A-12	HR25-9TP-12P(72)	1			NA28WSH-6P-100	12
HR25P-PT-A-16	HR25-9TP-16P(74)	1			NA28WSH-10P-100	16
HR25P-PT-A-20	HR25-9TP-20P(72)	1			NA28WSH-10P-100	20
HR25P-ST-A-4	HR25-7TP-4S(72)	1			NA28WSH-3P-100	4
HR25P-ST-A-6	HR25-7TP-6S(72)	1			NA28WSH-3P-100	6
HR25P-ST-A-8	HR25-7TP-8S(72)	1			NA28WSH-6P-100	8
HR25P-ST-A-12	HR25-9TP-12S(72)	1			NA28WSH-6P-100	12
HR25P-ST-A-16	HR25-9TP-16S(73)	1			NA28WSH-10P-100	16
HR25P-ST-A-20	HR25-9TP-20S(73)	1			NA28WSH-10P-100	20
HR25R-RP-A-8	HR25-7TR-8P(73)	1			NA28WSH-6P-100	8
HR25R-RP-A-12	HR25-9TR-12P(71)	1			NA28WSH-6P-100	12
HR25R-RP-A-4	HR25-7TR-4P(73)	1			NA28WSH-3P-100	4
HR25R-RP-A-6	HR25-7TR-6P(73)	1			NA28WSH-3P-100	6
HR25R-RP-A-16	HR25-9TR-16P(71)	1			NA28WSH-10P-100	16
HR25R-RP-A-20	HR25-9TR-20P(71)	1			NA28WSH-10P-100	20
HR25R-RS-A-8	HR25-7TR-8S(73)	1			NA28WSH-6P-100	8
HR25R-RS-A-12	HR25-9TR-12S(71)	1			NA28WSH-6P-100	12
HR25R-RS-A-4	HR25-7TR-4S(73)	1			NA28WSH-3P-100	4
HR25R-RS-A-6	HR25-7TR-6S(73)	1			NA28WSH-3P-100	6
HR25R-RS-A-16	HR25-9TR-16S(71)	1			NA28WSH-10P-100	16
HR25R-RS-A-20	HR25-9TR-20S(71)	1			NA28WSH-10P-100	20
HR25R-RPRT-A-4	HR25-7TR-4P(73)	1			NA28WSH-3P-100	4
HR25R-RPRT-A-6	HR25-7TR-6P(73)	1			NA28WSH-3P-100	6
HR25R-RPRT-A-8	HR25-7TR-8P(73)	1			NA28WSH-6P-100	8
HR25R-RPRT-A-12	HR25-9TR-12P(71)	1			NA28WSH-6P-100	12
HR25R-RPRT-A-16	HR25-9TR-16P(71)	1			NA28WSH-10P-100	16
HR25R-RPRT-A-20	HR25-9TR-20P(71)	1			NA28WSH-10P-100	20
HR25R-RSRT-A-4	HR25-7TR-4S(73)	1			NA28WSH-3P-100	4
HR25R-RSRT-A-6	HR25-7TR-6S(73)	1			NA28WSH-3P-100	6
HR25R-RSRT-A-8	HR25-7TR-8S(73)	1			NA28WSH-6P-100	8
HR25R-RSRT-A-12	HR25-9TR-12S(71)	1			NA28WSH-6P-100	12
HR25R-RSRT-A-16	HR25-9TR-16S(71)	1			NA28WSH-10P-100	16
HR25R-RSRT-A-20	HR25-9TR-20S(71)	1			NA28WSH-10P-100	20