

ハーネス部材表 ACサーボモータ対応ハーネス

シリーズ名	ハーネスタイプ	型式	コネクタ1型式	関連部材	コネクタ2型式	関連部材	使用圧着端子	A(C)ケーブル型式	B(D)ケーブル型式		
SV	電源 02092ページ	SVPK-SV1	-	-	J17-06FMH-7KL-1M-CF(取扱なし)	SJ1F-01GF-PO.8	RBG1.25-4RE	NA3CT-20-4(04711)	NA3CTR-22-4(04712)		
		SVPK-SV2	-	-	J27-06FMH-7KL-1M-CF(取扱なし)	SJ2F-01GF-P1.0	RBG1.25-4RE	NA3CT-20-4(04711)	NA3CTR-22-4(04712)		
		SVPK-SV3	-	-	J37-06FMH-8KL-1L-CF(取扱なし)	SJ3F-41GF-P1.8	RBG1.25-4RE	NA3CTF-T(04711)	NA3CTR-R(04712)		
		SVPK-SV4	-	-	NMS3106B18-10S(03209)	NMS3057-10A	-	NAV3CT-2-4(04105)	NARVCT-2-4(04409)		
		SVPK-SV5	-	-	NMS3106B18-10-S(03209)	-	-	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
		SVPK-SV6	-	-	NMS3106B-22-22-S(03209)	-	-	NA6CT-10-4(04711)	NA6CTR-10-4(04712)		
		SVPK-SV7	-	-	NMS3106B-22-22-S(03209)	-	-	NA6CT-8-4(04711)	NA6CTR-8-4(04712)		
		SVPK-SV1B	-	-	J17-06FMH-7KL-1M-CF(取扱なし)	SJ1F-01GF-PO.8	RBG1.25-4RE	NA3CT-20-6(04711)	NA3CTR-22-6(04712)		
		SVPK-SV2B	-	-	J27-06FMH-7KL-1M-CF(取扱なし)	SJ2F-01GF-P1.0	RBG1.25-4RE	NA3CT-20-6(04711)	NA3CTR-22-6(04712)		
		SVPK-SV3B	-	-	J37-06FMH-8KL-1L-CF(取扱なし)	SJ3F-41GF-P1.8	RBG1.25-4RE	NA3CTF-T(04711)	NA3CTR-F(04712)		
		SVPK-SV4B	-	-	CM10-SP2S-M-D(03354)	CM10-#22SD(S2)(D8)-100	-	NAV3PB-8	-		
		エンコーダ 02093ページ	SVEK-SV1	55100-0670(取扱なし)	-	54346-0070(取扱なし)	-	-	NA20276TSB-A(04713)	NA20276RRSB-C(04713)	
		SVEK-SV2	55100-0670	-	CM10-SP10S-M-D(03354)	CM10-#22SD(S2)(D8)-100	-	-	NA20276TSB-A(04713)	NA20276RRSB-C(04713)	
		MV	電源 02095ページ	SVPP-MV1	-	RBV1.25-PR	172159-1(03429)	171638-1(171636-1)03429	-	NAV3PR-A(04714)	-
SVPP-MV1B	-			RBV1.25-PR	172157-1(03429)	170364-1(170363-1)03429	-	NAV3BR-A(04714)	-		
エンコーダ 02096ページ	SVEK-MV1		55100-0670(取扱なし)	-	172161-1(03429)	170363-1(170359-1)03429	-	NAMFSB-25-3P(04714)	-		
	SVEK-MV1		55100-0670(取扱なし)	-	172161-1(03429)	170363-1(170359-1)03429	-	NAMFSB-25-3P(04714)	-		
MINAS A5	電源 02097ページ	SVPP-A51	A10.75-8GY(挿着)	N1.25-M4(丸端子)	JN8FT04S1	ST-TMH-S-C18-3500	-	NA3CT-20-4(04711)	NA3CTR-20-4(04712)		
		SVPP-A52	-	-	JL04V-6A20-4SE-EB-R(03310)	-	-	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-A53	-	-	JL04V-6A22-22SE-EB-R(03310)	-	-	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-A54	-	-	JL04V-6A22-22SE-EB-R(03310)	-	-	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
	ブレーキ用 02097ページ	SVPP-A51B	N1.25-M4(丸端子)	-	JN4FT02SJM-R	ST-TMH-S-C18-3500	-	NA3VC-19-2	NA3MF-19-2		
		SVPP-A52B	-	-	JL04V-6A20-18SE-EB-R(03310)	-	-	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-A53B	-	-	JL04V-6A24-11SE-EB-R(03310)	-	-	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-A54B	-	-	JL04V-6A24-11SE-EB-R(03310)	-	-	NA6CT-10-4(04711)	NA6CTR-10-4(04712)		
	エンコーダ用 02099ページ	SVEP-A52	55100-0670(取扱なし)	-	JN6FR079M1(取扱なし)	LY10-C1-A1-10000	-	NA20276TSB-C(04713)	NA20276RRSB-E(04713)		
		SVEP-A52	55100-0670(取扱なし)	-	JN2DS10SL1-R(取扱なし)	-	-	NA3VCSB-25-3P(04311)	NA3MFSB-25-3P(04511)		
MINAS A4	モータ 02100ページ	SVPP-MIA41	-	-	JL04V-6A20-4SE-EB-R(03310)	JL04-2022CK-14	N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-MIA41S	-	-	JL04V-6A20-4SE-EB-R(03310)	JL04-2022CK-14	(R)N2-M4(挿)A2.5-8BU	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-MIA42	-	-	JL04V-6A22-22SE-EB-R(03310)	JL04-2022CK-14	N5.5-S4	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
		SVPP-MIA43S	-	-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	(R)N2-M4(挿)A2.5-8BU	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-MIA44	-	-	JL04V-6A24-11SE-EB-R(03310)	JL04-2428CK-17	N5.5-S4	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
		SVPP-MIA45S	-	-	172159-1(03429)	170366-1	(R)N1.25M4(挿)A1.5-8BK	NA6CT-18-4(04711)	NA6CTR-18-4(04712)		
		SVPP-MIA41B	-	-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	(1.8AWG)N1.25-M4(1.4AWG)N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
		SVPP-MIA41BS	-	-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	(1.8AWG)A2.5-8BU(1.4AWG)A2.5-8BU N2-M4	NA6CT-18-2(04203)	NA6UCR-18-2(04417)		
		SVPP-MIA42B	-	-	JL04V-6A24-11SE-EB-R(03310)	JL04-2428CK-17	(1.8AWG)N1.25-M4(1.4AWG)N2-M4	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
		SVPP-MIA43B	-	-	172157-1(03429)	170366-1	N1.25-M4	NA6UC-18-2(04203)	NA6UCR-18-2(04417)		
	エンコーダ 02101ページ	SVEP-MIA41	55100-0670(取扱なし)	-	172160-1(03429)	170365-1	-	NAVCSB-25-3P(04327)	NAMFSB-25-3P(04535)		
		SVEP-MIA42	55100-0670(取扱なし)	-	NMS3106B-20-29-S(03209)	NMS3057-12A	-	NAVCSB-25-3P(04327)	NAMFSB-25-3P(04535)		
		MINAS AIII	モータ 02104ページ	SVPP-MIA31	-	-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)
				SVPP-MIA31D	-	-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	(R)N2-M4(挿)A2.5-8BU	NA6CT-14-4(04711)	NA6CTR-14-4(04712)
SVPP-MIA32	-			-	JL04V-6A24-11SE-EB-R(03310)	JL04-2428CK-17	N5.5-S4	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
SVPP-MIA33D	-			-	172159-1(03429)	170366-1	(R)N1.25M4(挿)A1.5-8BK	NA6CT-18-4(04711)	NA6CTR-18-4(04712)		
SVPP-MIA34	-			-	JL04V-6A20-4SE-EB-R(03310)	JL04-2022CK-14	N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
SVPP-MIA34D	-			-	JL04V-6A20-4SE-EB-R(03310)	JL04-2022CK-14	(R)N2-M4(挿)A2.5-8BU	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
SVPP-MIA35	-			-	JL04V-6A22-22SE-EB-R(03310)	JL04-2022CK-14	N5.5-S4	NA6CT-12-4(04711)	NA6CTR-12-4(04712)		
SVPP-MIA31B	-			-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	(1.8AWG)N1.25-M4(1.4AWG)N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
SVPP-MIA31BD	-			-	JL04V-6A20-18SE-EB-R(03310)	JL04-2022CK-14	(1.8AWG)A2.5-8BU(1.4AWG)A2.5-8BU N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
SVPP-MIA32B	-			-	JL04V-6A24-11SE-EB-R(03310)	JL04-2428CK-17	(1.8AWG)N1.25-M4(1.4AWG)N2-M4	NA6CT-14-4(04711)	NA6CTR-14-4(04712)		
エンコーダ 02106ページ	SVEP-MIA31	10120-3000PE(03072)	-	172160-1(03429)	170365-1	-	NAVCSB-25-4P(04327)	NAMFSB-25-4P(04535)			
	SVEP-MIA32	10120-3000PE(03072)	-	NMS3106B-20-29-S(03209)	NMS3057-12A	-	NAVCSB-25-4P(04327)	NAMFSB-25-4P(04535)			