


V GUIDES SYSTEM -UNITS-WHEELS / 90° TYPE- Vガイド -90°タイプ ユニット品/ホイール-

価格改訂

- ：値下げ価格
- ：新価格
- ：スライド値引変更


大口対応
BIG ORDER

CADデータフォルダ名：09_Slide_Rails



Type	No.	A	B	d	D		MDW		(G)*	(H)*	K	ラジアル荷重 (LRmax.) (N)	スラスト荷重 (LSmax.) (N)	¥基準単価
BVGH	1	19.557	7.874	4.762	15.848	7.924	11.861	1.0	0.5		1220	252	2,110	
	2	30.733	11.099	9.525	25.399	12.700	18.236	1.4	0.7		2650	625	2,340	
	3	45.718	15.874	11.999	38.099	19.049	26.974	2.0	1.0		5900	1701	3,450	
BVGHS	1	19.557	7.874	4.762	15.848	7.924	11.861	1.0	0.5	0.229	1220	252	3,450	
	2	30.733	11.099	9.525	25.399	12.700	18.236	1.4	0.7		2650	625	3,910	
	3	45.718	15.874	11.999	38.099	19.049	26.974	2.0	1.0		5900	1701	6,050	
BVGHT	1	19.557	7.874	4.762	15.848	7.924	11.861	0.508	0.254		1013	209	4,050	
	2	30.733	11.099	9.525	25.399	12.700	18.236	0.762	0.381		2200	519	4,790	
	3	45.718	15.874	11.999	38.099	19.049	26.974	0.889	0.432		4897	1412	7,830	

kgf=N×0.101972




Type	No.	仕様	L	D	B	d	許容差	適用ボルト	X	l1	H	¥基準単価
BVGBS	1	C	13.68	4.75	10	3	+0.014 0	M3	—	6.06	10	580
	2	C	17.24	9.52	13	6	+0.018 0	M6	—	6.45	12	790
	3	C	24.68	11.99	19	8	+0.022 0	M8	—	9.06	17	1,290

Order 注文例: 型式 - 仕様
BVGBS1 - E
SF-BVGBS1 - C

Delivery 出荷日: 在庫品 翌日出荷 P.133

Price 価格: 数量スライド価格 (P.133)



Type	No.	L	E	F	G	J	MD	D	B1	N	P
BVGTLN1	1	90~1790	±0.38	±0.38	±0.05	1.57	3.18	3.5	4	20	50
	2	(寸法は価格表を参照ください)	15.88	6.35	0.79	2.36	4.75	4.5	5.5		
	3		22.23	8.71	1.57	2.77	6.35	5.5	8		

Order 注文例: 型式 - L
BVGTLN1 - 640
SF-BVGTLN2 - 390

Delivery 出荷日: 3 日日出荷

Price 価格: 数量スライド価格 (P.133)


片刃トラック

L	BVGTLN1	BVGTLN2	BVGTLN3	BVGTLN4	BVGTLN5
90・140・190	3,010	3,190	4,290	3,620	4,160
240・290	3,860	4,120	6,280	4,760	5,590
340・390	4,700	5,050	8,270	5,900	7,010
440・490	5,550	5,980	10,260	7,060	8,420
540・590	6,390	6,910	12,250	8,200	9,840
640・690	7,240	7,840	14,240	9,350	11,250
740・790	8,080	8,770	16,220	10,500	12,680
840・890	8,940	9,710	18,210	11,640	14,100
940・990	9,770	10,640	20,200	12,790	15,510
1040・1090	10,630	11,580	22,190	13,940	16,930
1140・1190	11,460	12,500	24,180	15,080	18,350
1240・1290	13,250	13,940	26,610	17,260	20,640
1340・1390	14,260	15,000	28,720	18,570	22,270
1440・1490	15,260	16,070	30,840	19,870	23,900
1540・1590	16,270	17,140	32,950	21,180	25,540
1640・1690	17,280	18,190	35,060	22,490	27,170
1740・1790	19,130	19,260	37,170	23,800	28,800

V GUIDES SYSTEM -BUSHINGS TRACK / 90° TYPE- Vガイドシステム -90°タイプ ブッシュ/片刃トラック/両刃トラック-


ステンレス・めっき品
脱脂洗浄サービス
対応商品詳細は下記URL
http://fa.misumi.jp

CADデータフォルダ名：09_Slide_Rails



両刃トラック

Type	No.	L (選択)	W	W1	T	N ±1.0	P ±0.2	d
BVGUR25	25	90~1740	(25)	25.74	4.5	20	50	5.5
	44	(寸法は価格表を参照ください)	(44)	44.74	6.0			7.0



Type	No.	L (選択)	W	W1	d	A	B	X1	X2	Y1	Y2	d1	d2	E	F	H	T	ホイール	ボルト
BVGU (1キャリアジ)	25	90~1740	25	25.74	5.5	80	70	70	40	50	41.59	M5	M3	10	10	17.5	4.5	BVGH1	CB3-22
	25L	(寸法は価格表を参照ください)	25	25.74	5.5	120	70	100	80	50	41.59	M5	M3	10	10	17.5	4.5	BVGH1	CB3-22
BV2GU (2キャリアジ)	44		44	44.74	7	120	105	100	80	80	70.14	M6	M6	10	12	24.5	6	BVGH2	CB6-25

L (選択)	BVGU25	BV2GU25	BVGU25L	BV2GU25L	BVGU44	BV2GU44
90	20,470	—	—	—	—	—
140	20,470	—	23,410	—	30,720	—
190・240	24,880	37,020	27,690	—	39,270	—
290・340	29,280	41,330	31,960	46,580	47,830	65,590
390・440	33,680	45,640	36,220	50,760	56,380	73,970
490・540	38,100	49,980	40,510	54,960	64,950	82,360
590・640	42,500	54,290	44,780	59,150	73,500	90,740
690・740	46,910	58,610	49,060	63,340	82,060	99,130
790・840	51,310	62,920	53,330	67,530	90,610	107,510
890・940	55,730	67,250	57,610	71,720	99,170	115,900
990・1040	60,130	71,560	61,890	75,920	107,730	124,290
1090・1140	66,700	78,000	68,250	82,150	116,280	132,670
1190・1240	73,090	84,270	75,730	89,480	129,120	145,250
1290・1340	77,740	88,820	80,390	94,050	138,410	154,350
1390・1440	82,840	93,820	85,490	99,040	147,710	163,470
1490・1540	87,720	98,600	90,360	103,820	156,990	172,560
1590・1640	92,590	103,380	95,240	108,600	166,280	181,670
1690・1740	97,460	108,150	100,110	113,370	175,570	190,770

Order 注文例: 型式 - L
BVGU25 - 840

Delivery 出荷日: 3 日日出荷

Price 価格: 数量スライド価格 (P.133)