

SPROCKETS -SP SERIES- 標準スプロケット -SPシリーズ-



■特長：自由に追加加工可能な軸穴粗加工品(軸穴仕様[S])もお選びいただけます。

●CADデータフォルダ名：21_Chains_and_Sprockets

Technical drawing of a sprocket with dimensions and material specifications. Includes a table for Type (SP□□B) and Material (S45C相当), and diagrams for shaft hole types S (rough) and N (JIS). Dimensions include Dp, Do, H, GD, L, l, X, Z, and mass (g).

■適合チェーン選定方法 P.1652

チェーン伝動機構の技術情報 P.2445

Main sprocket selection table with columns for Type, Pitch, Sprocket Type, Teeth, Shaft Hole Type, Shaft Hole Size, Dimensions (Dp, Do, H, GD, L, l, X, Z), Mass (g), and Chain Standards. It lists various sprocket models and their compatibility with different chain types.

Detailed sprocket specifications table for various models (SP 50, 60, 80) and shaft hole types (S, N). It provides specific dimensions and mass values for each configuration.

■軸穴加工寸法表

Table showing shaft hole processing dimensions for different sprocket models, including pitch, keyway width, and set screw diameter.

※下記の商品はセットスクリーナのサイズが変わります。

Table showing set screw sizes for different sprocket models and shaft hole types.

Order and delivery information section. Includes order form fields for model (SP35B16), shaft hole type (N), and pitch (10). Delivery options include '在庫品' (in stock) and '翌日出荷' (next day shipping).

Price and quantity information section. Includes a table for quantity discounts and delivery dates. Notes indicate that prices are for standard quantities and that delivery dates are subject to change.

21 チェーン スプロケット

SPROCKETS -BSP SERIES-
標準プロケット
 -BSPシリーズ-



■特長: 黒染めタイプを標準品としてご用意しております。

◎CADデータフォルダ名: 21_Chains_and_Sprockets

Type	M 材質	S 表面処理
BSP□□B	S45C相当 (歯先高周波焼入)	四三酸化鉄被膜

△付属品 セットスクリーン

◎歯先とキー溝のスレは±0.5mm

軸穴仕様 **N**
(新JISキー+タップ)

■適合チェーン選定方法 P.1652

チェーン伝動機構の技術情報 P.2445

型式			軸穴径(D)												Y基準単価																											
Type	呼び	ボスタイプ	歯数	軸穴仕様	S仕様	N仕様(H7) ※は在庫品												Dp	Do	H	GD	L	ℓ	X	Z	質量(g)	S仕様	N仕様														
			N仕様(H7) ※は在庫品																																							
BSP	35	B	N	-	-	10 10K	27.85	32	21.5	17													60	-	800	890													200	-	-	1,130
						10 10K* 12*	30.82	34	24.5	20													80	-	800	890													270	-	-	1,130
						10 10K* 12	33.81	38	27	23													90	-	800	890													330	-	-	1,150

型式			軸穴径(D)												Y基準単価																											
Type	呼び	ボスタイプ	歯数	軸穴仕様	S仕様	N仕様(H7) ※は在庫品												Dp	Do	H	GD	L	ℓ	X	Z	質量(g)	S仕様	N仕様														
BSP	50	B	N	-	-	16 17 18 19	46.42	53	34	29													200	-	-	1,130													200	-	-	1,130

②チェーンプロケット

■軸穴加工寸法表

軸穴径 D	キー溝 b²×ℓ²	セットスクリーン M
10	3×1.4	4
10K・12	4×1.8	5
14~17	5×2.3	6
18~22	6×2.8	6
24~30	8×3.3	8
32~38	10×3.3	8
40・42	12×3.3	8
45・50	14×3.8	10



Order 注文例

型式 軸穴仕様 軸穴径
 BSP35B16 - N - 10



Delivery 出荷日

●アスタリスク(*)が付いている製品
 在庫品 翌日出荷 P.133
 ◎ご希望によりPM6:00迄、当日出荷受付致します。

●アスタリスク(*)のない製品
5 日目出荷



Price 価格

●N仕様
 ■数量スライド価格 (1円未満切り捨て) P.133
 数量区分 標準対応 個別対応
 数量 1~9 10~14 15~20 21~50 51~
 値引率 基準単価 5% 10% 20% お見積り
 出荷日 通常 +2日 お見積り

●S仕様
 ■数量スライド価格 (1円未満切り捨て) P.133
 数量区分 標準対応 個別対応
 数量 1~9 10~14 15~20 21~50 51~
 値引率 基準単価 10% 20% 30% お見積り
 出荷日 通常 +2日 お見積り

◎表示数量超えはWOSにてご確認ください。

SPROCKETS -SSP SERIES- / DOUBLE SPROCKETS -40SD・50SD SERIES-

標準スプロケット/2列スプロケット

-SSPシリーズ- -40SD・50SDシリーズ-



CADデータフォルダ名: 21_Chains_and_Sprockets

CADデータフォルダ名: 21_Chains_and_Sprockets

特長: 自由に追加加工可能な軸穴粗加工品(軸穴仕様S)もお選びいただけます。

Technical drawing of a sprocket showing dimensions (Dp, Do, H, GD, L, l, X, Z) and material options (Type SSP, SUS304). Includes a RoHS 10 logo and a note about keyway fit.

適合チェーン選定方法 P.1652

チェーン伝動機構の技術情報 P.2445

Main sprocket selection table with columns for Type, Pitch, Teeth, Sprocket Type, Pitch Circle Diameter (Dp), Outer Diameter (Do), Height (H), Groove Depth (GD), Length (L), Keyway Depth (l), Keyway Width (X), Keyway Position (Z), Weight (g), and Price. It lists various models like SSP 25, 35, 40 and their specifications.

Detailed sprocket selection table for models SSP 50 and SSP 60, showing a wide range of tooth counts and their corresponding dimensions and weights.

Technical drawing of a sprocket with a keyway and a table of keyway dimensions (D, b, M) for different sprocket sizes.

Order and price information section including 'Order 注文例' (SPP35B17), 'Delivery 出荷日' (3 days), and 'Price 価格' (quantity discounts).

特長: 2本のチェーンに動力を伝達するスプロケット。多軸駆動装置にご利用いただけます。

Technical drawing of a double sprocket (2列スプロケット) with dimensions and material options (Type SP, S45C equivalent).

適合チェーン選定方法 P.1652

Double sprocket selection table with columns for Type, Pitch, Teeth, Sprocket Type, Pitch Circle Diameter (Dp), Outer Diameter (Do), Height (H), Length (L), Keyway Width (X), Keyway Position (Y), Weight (kg), and Price. Lists models like SP 40 and SP 50.

21 チェーン スプロケット