



ROTARY SHAFTS -RETAINING RING GROOVES ON BOTH ENDS WITH KEY GROOVES-


回転軸 -D公差 h9(みがき棒)/h7(研磨棒)/g6(研磨棒)-

-止め輪溝・キー溝付タイプ-

キー溝加工を1~3ヶ所までご選択いただけます。



Table with columns: Type, 標準タイプ, 止め輪付タイプ, D公差, 材質, S表面処理



D部面相度 h9(みがき棒)は、h7(研磨棒)・g6(研磨棒)は、になります。




Table for h9 (keyed) specifications, including Type, D公差, L, F・S, and keyway options

Table for h7 (ground) specifications, including Type, D公差, L, F・S, and keyway options

Table for g6 (ground) specifications, including Type, D公差, L, F・S, and keyway options

Order information, delivery date (2 days), and contact details

Price adjustment and quantity discount information

2-day delivery and large order information

CADデータフォルダ名: 12_Rotary_Shafits

Price table with columns: 数量区分, 小口, 大口, 個別対応

製品価格は表中価格にキー溝加工代を加えた金額になります。

Large table for h9 (keyed) types, including SUS304 and stainless steel options

Large table for h7 (ground) types, including SUS304 and stainless steel options

Table for h9 (keyed) types, including SUS304 and stainless steel options

Table for h7 (ground) types, including SUS304 and stainless steel options

Table for g6 (ground) types, including SUS304 and stainless steel options

Additional specifications and contact information

12 回転軸