

HIGH PRECISION XY-AXIS CROSSED ROLLER -THIN/THRU HOLE-

【高精度】XY軸クロスローラ

一薄型/透過穴



- 値下げ価格
新価格
スライド引率変更

ステージに関するよくあるお問い合わせはこちら P.2078

CADデータフォルダ名: 28_Stage5

特長: XY軸の一体構造により、XYPG(P.2133)と比べてさらなる薄型化を実現。XY軸は厚さ28mm以下に抑えられ、直交出しも不要です。



Material and specifications table for XY axis thin type

特長: 中央にφ50mmの透過穴を設けております。真下から光を照射させながら微調整することなどが可能です。



Material and specifications table for XY axis through hole

標準ステージ類似品: XYCRSC(P.2134)、一部サイズのみ。

Performance comparison table for XY axis stages

マイクロメータヘッド最小読取10μm/目盛

Order and delivery information section including pricing and lead times

Alterations section showing options for micro-meter head position and clamping

- Micro-meter head or clamp mounting method
Handle diameter extension
Extension of micro-meter head handle

HIGH PRECISION XY-AXIS LINEAR BALL GUIDE -MICROMETER HEAD/FEED SCREW-

【高精度】XY軸リニアボール

マイクロメータヘッド/送りねじ



- 値下げ価格
新価格
スライド引率変更

ステージに関するよくあるお問い合わせはこちら P.2078

CADデータフォルダ名: 28_Stage5

特長: 高精度・高剛性を実現したステージです。2軸にしても厚さ40mm以下に抑えられ、直交出しも不要です。

XY axis product image and RoHS 10 certification

Micro-meter head and feed screw product images and technical drawings

Micro-meter head (XYSG, XYSCGB) and feed screw (XYSCG, XYSCGB) specifications table

Performance table for micro-meter head and feed screw

Order and delivery information for micro-meter head and feed screw

Alterations section for micro-meter head and feed screw, including clamping and headless options

Additional notes and specifications for micro-meter head and feed screw

28 ステージユニット