



COLLARS -D-V TOLERANCE SPECIFIED TYPE-

金属カラー

一並級 内外径公差選択・寸法フリー指定タイプ

2日目納短縮

価格改訂

大口対応 BIG ORDER

新価格

カタログ規格外品はこちら P.137

CADデータフォルダ名: 33_Washers

Technical specifications including material options (S45C, 2000 series Al, SUS304, SUS316), surface treatments, and tolerance tables for D, V, and L dimensions. Includes a diagram of the collar and a note about RoHS 10.

Main price table with columns for material type (SNCAB, SNCBB, SNCS, SNCSSR, SNCSUS), tolerance selection (D, V), and length (L). Rows show price per unit for various diameter and length ranges.

Notes explaining the relationship between D, V, and L tolerances, and providing a diagram for H7 effective length.

Order form showing selection options for material (SNCAB), tolerance (G, H), length (V10.0), diameter (D25), and length (L50.5).

Delivery and payment information, including delivery dates and payment terms for different material types.

Price information section detailing quantity discounts and price per unit for different materials.

Price table showing standard and special prices for different quantities and materials.

Alteration form for specifying changes to the collar's dimensions and materials.

Alterations table showing the effect of changing L, LCB, LCC, LCD, or LCE on the collar's dimensions.

Large price table for standard materials (SNCB, SNCM, SNCR, SNCAN, SNCAA) with columns for diameter, length, and price per unit.

Notes for standard materials regarding tolerance selection and effective length.

Order form for standard materials, showing selection options for material (SNCC), tolerance (G, H), length (V10.0), diameter (D25), and length (L50.5).

33 Washer シム



COLLARS -D-V TOLERANCE SPECIFIED TYPE-

金属カラー

精密級 内外径公差選択・寸法フリー指定タイプ

カタログ規格外品はこちら P.137

CADデータフォルダ名: 33_Washers

2日目納期短縮, 価格改訂, 大口対応 BIG ORDER



Table with columns: 型式, M材質, S表面処理


Table with columns: D, G, H, N, X, V, H, N, X

Table with columns: V, H, N, X

加工条件
*1 肉厚と全長の加工限界
*2 肉厚と全長の加工限界(材質200系7%合金・黄銅)

内外径公差価格番号表

価格表の見方
例>材質S45C相当、外径g6、内径H7、L公差±0.01を注文する場合



D=16以下 C0.1~0.2
D=16.5以上 C0.5以下

Main price table with columns: 型式, D公差, V公差, V, D, L, SNMC, SNMB, SNMM, SNMR

D・V公差にGまたはHを選択した場合は、D≥9の適用となります。
またその場合、Vの指定範囲は下表となります。

Price table for SUS316 and SUS304 materials with columns: 型式, D公差, V公差, V, D, L, SNMS, SNMSR, SNMSUR

D・V公差にGまたはHを選択した場合は、D≥9の適用となります。
またその場合、Vの指定範囲は下表となります。

Order注文例: SNMS - G H - V100 - D25 - L505

Delivery出荷日: ストックA早割, ストックA

Price価格: 数量スライド価格, 標準対応

Alteration追加加工: SNMS - G H - V100 - D25 - L500 - LCB

Alterations table with columns: Code, マイナス公差変更, プラス公差変更, ゼロ・マイナス公差変更, ゼロ・プラス公差変更

カラー・シム