


METAL BLOCKS STANDARD TYPE -0.1mm SPECIFICATION OF DIMENSION-

金属ブロック 標準タイプ


-全角直角度保証0.1mm単位指定-



材料屋24でミス型番・出荷日・価格を一発表示!



型式	材質	硬度
SSFB	SS400	-
SCFB	S50C	-
SCNFB	S50C調質	25±3HRC
SCFF	SUS303	-
SCFS	SUS304	-



SCNFBは板厚によっては硬度が落ちる場合があります。
6面フライス

0.1mm単位		T 0.1mm単位				
A	B	1.5~9.9		5.0~9.9		
		SSFB	SCFB	SCNFB	SCFF	SCFS
60	10.0~60.0	950	1,020	1,360	1,700	2,300
100	10.0~60.0	1,000	1,080	1,420	2,090	2,610
60	60.1~100.0	1,000	1,080	1,420	-	-
100	60.1~100.0	1,110	1,280	1,730	-	-

0.1mm単位		T 0.1mm単位														
A	B	10.0~20.0					20.1~30.0					30.1~40.0				
		SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SCNFB	SCFF	SCFS
10.0~60.0	10.0~60.0															
60.1~100.0																
100.1~130.0																
130.1~160.0																
160.1~180.0																
180.1~200.0	20.0~60.0															
200.1~250.0																
250.1~300.0																
300.1~350.0																
350.1~400.0																
400.1~450.0	60.1~100.0															
450.1~500.0																
10.0~60.0																
60.1~100.0																
100.1~130.0																
130.1~160.0	100.1~130.0															
160.1~180.0																
180.1~200.0																
200.1~250.0																
250.1~300.0																
300.1~350.0	130.1~160.0															
350.1~400.0																
400.1~450.0																
450.1~500.0																
10.0~60.0																
60.1~100.0	160.1~180.0															
100.1~130.0																
130.1~160.0																
160.1~180.0																
180.1~200.0																
200.1~250.0	180.1~200.0															
250.1~300.0																
300.1~350.0																
350.1~400.0																
400.1~450.0																
450.1~500.0																

Web 金額はWOSにてご確認ください。

Web 金額はWOSにてご確認ください。

SCFFのみT寸55.0mmまでとなります。

Order 注文例 型式 A - B - T
SCFB - 30.5 - 20.6 - 17.1

Delivery 出荷日 3 日目出荷 ストック A 翌日出荷 800円/1本 PM 6:00迄 P.134

3本以上で1明細行当たり一律2,160円

- SSFB・SCFB
20個以上は納期が変わる可能性があります。
- SCNFB・SCFF・SCFS
21個以上は納期が変わる可能性があります。

Price 価格 WOSにてご確認ください。

項目	精度基準 (最大値)	
	SS400 S50C S50C調質	SUS303 SUS304
板厚平行度 (100mmに対して)	0.02	0.05
平面度 (100mmに対して)	T1.5~7.9	0.1
	T8~15.9	0.07
	T16~	0.05
直角度 (各面)	100mmに対し0.02	
全周面取り	C0.5以下	

0.1mm単位		T 0.1mm単位																							
A	B	40.1~50.0					50.1~60.0					60.1~70		70.1~80		80.1~90		90.1~100							
		SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SCNFB	SCFF	SCFS	SSFB	SCFB	SSFB	SCFB	SSFB	SCFB	SSFB	SCFB	
10.0~60.0	10.0~60.0																								
60.1~100.0																									
100.1~130.0																									
130.1~160.0																									
160.1~180.0																									
180.1~200.0	20.0~60.0																								
200.1~250.0																									
250.1~300.0																									
300.1~350.0																									
350.1~400.0																									
400.1~450.0	60.1~100.0																								
450.1~500.0																									
10.0~60.0																									
60.1~100.0																									
100.1~130.0																									
130.1~160.0	100.1~130.0																								
160.1~180.0																									
180.1~200.0																									
200.1~250.0																									
250.1~300.0																									
300.1~350.0	130.1~160.0																								
350.1~400.0																									
400.1~450.0																									
450.1~500.0																									
10.0~60.0																									
60.1~100.0	160.1~180.0																								
100.1~130.0																									
130.1~160.0																									
160.1~180.0																									
180.1~200.0																									
200.1~250.0	180.1~200.0																								
250.1~300.0																									
300.1~350.0																									
350.1~400.0																									
400.1~450.0																									
450.1~500.0																									