




TENSION SPRINGS

引張りばね

—フリー指定タイプ—



型式 Type	D	線径 dmm	S指定 1mm単位	基準最大タワミ mm		基準ばね定数 N/mm		初張力 N	
				WFSP BWFSP	UFSP BUFSP	WFSP BWFSP	UFSP BUFSP	WFSP BWFSP	UFSP BUFSP
WFSP UFSP BWFSP BUFSP	3	0.3	10~300	88	87	0.025	0.021	0.18	0.21
		0.4		41	42	0.12	0.10	0.53	0.64
		0.5		48	46	0.15	0.13	0.77	0.92
	4	0.4	10~500	86	87	0.04	0.04	0.31	0.38
		0.5		48	46	0.15	0.13	0.77	0.92
		0.6		84	82	0.07	0.06	0.49	0.59
		0.7		50	51	0.18	0.16	1.01	1.21
		0.8		79	82	0.10	0.09	0.71	0.85
		0.9		36	36	0.47	0.41	2.13	2.55
	5	0.6	10~550	70	66	0.13	0.12	0.96	1.15
		0.7		35	32	0.52	0.45	2.94	3.5
		0.8		74	76	0.18	0.16	1.26	1.51
		0.9		41	42	0.58	0.51	3.04	4.26
		1.0		56	57	0.39	0.34	2.45	3.43
		1.1		33	33	1.05	0.93	4.41	6.17
	6	1.0	10~550	74	70	0.27	0.24	1.96	2.74
		1.1		44	43	0.73	0.65	4.31	6.03
		1.2		29	28	1.70	1.50	7.64	10.7
		1.3		80	76	0.20	0.17	1.45	2.01
		1.4		46	45	0.53	0.47	3.24	4.51
		1.5		31	30	1.24	1.08	6.39	8.87
	7	1.0	10~550	116	113	0.15	0.13	1.18	1.65
		1.1		71	70	0.39	0.35	2.84	3.98
		1.2		46	46	0.91	0.80	5.39	7.55
1.3		31		30	1.88	1.66	8.72	12.21	
1.4		120		117	0.11	0.10	0.93	1.29	
1.5		72		71	0.31	0.27	2.17	3.01	
8	1.2	10~550	47	47	0.70	0.61	3.95	5.49	
	1.3		32	31	1.42	1.24	7.75	10.76	
	1.4		104	96	0.24	0.21	2.06	2.88	
	1.5		69	65	0.54	0.48	3.82	5.35	
	1.6		47	45	1.11	0.98	6.66	9.32	
	1.7		34	33	2.10	1.86	10.6	14.84	
9	1.2	10~550	106	98	0.19	0.17	1.50	2.09	
	1.3		70	66	0.43	0.38	3.03	4.21	
	1.4		48	46	0.88	0.76	4.74	6.59	
	1.5		35	34	1.69	1.47	9.25	12.85	
	1.6		96	91	0.35	0.31	3.04	4.26	
	1.7		66	65	0.71	0.63	5.10	7.14	
10	1.2	10~550	48	47	1.33	1.18	8.33	11.66	
	1.3		34	35	2.37	2.10	12.60	17.64	
	1.4		97	92	0.29	0.25	2.21	3.08	
	1.5		67	66	0.58	0.50	4.03	5.60	
	1.6		49	48	1.11	0.97	6.74	9.37	
	1.7		35	36	1.98	1.73	10.90	15.13	
11	1.2	10~550	88	87	0.48	0.42	4.02	5.63	
	1.3		64	64	0.90	0.80	6.47	9.06	
	1.4		47	48	1.59	1.40	10.00	14.00	
	1.5		31	30	3.40	3.01	18.70	26.18	
	1.6		84	78	0.63	0.56	5.10	7.14	
	1.7		61	60	1.11	0.99	7.94	11.12	
12	1.2	10~550	41	40	2.37	2.10	15.20	21.28	
	1.3		29	29	4.64	4.10	23.60	33.04	
	1.4		75	74	0.81	0.72	7.35	10.30	
	1.5		53	52	1.72	1.52	11.80	16.50	
	1.6		37	37	3.35	2.96	19.60	27.40	
	1.7		27	27	6.09	5.39	33.30	46.60	
13	1.2	10~550	72	72	1.12	0.99	9.80	13.70	
	1.3		50	52	2.17	1.92	15.70	22.00	
	1.4		38	36	3.93	3.48	22.50	31.50	
	1.5		28	27	6.75	5.97	34.30	48.00	
	1.6		69	64	1.49	1.32	12.70	17.80	
	1.7		51	49	2.69	2.38	17.60	24.60	
14	1.2	10~550	39	37	4.58	4.05	27.40	38.40	
	1.3		31	29	7.49	6.62	39.20	54.90	
	1.4								



■数量スライド価格 (●1円未満切り捨て) P.133

数量区分	標準対応				個別対応
	小口	大口	大口	大口	
数量	1~9	10~14	15~19	20~30	31~
値引率	基準単価	10%	20%	35%	お見積り

●表示数量超えはWOSにてご確認ください。

D	d	¥基準単価						¥基準単価							
		WFSP			BUFSP			UFSP			BUFSP				
		S10 ~20	S21 ~50	S51 ~100	S101 ~200	S201 ~300	S301 ~450	S451 ~550	S10 ~20	S21 ~50	S51 ~100	S101 ~200	S201 ~300	S301 ~450	S451 ~550
3	0.3	450	540	610	880	1,100	—	—	550	700	780	1,140	1,430	—	—
	0.4	450	540	610	880	1,100	—	—	550	700	780	1,140	1,430	—	—
	0.5	450	540	610	880	1,100	—	—	550	700	780	1,140	1,430	—	—
4	0.4	450	540	610	880	1,100	—	—	550	700	780	1,140	1,430	—	—
	0.5	450	540	640	950	1,190	1,360	1,810	550	700	830	1,220	1,540	1,750	2,170
	0.6	450	540	640	950	1,190	1,360	1,810	550	700	830	1,220	1,540	1,750	2,170
5	0.5	450	540	640	950	1,190	1,360	1,810	550	700	830	1,220	1,540	1,750	2,170
	0.6	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
	0.7	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
6	0.6	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
	0.7	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
	0.8	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
7	0.7	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
	0.8	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
	0.9	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
8	0.8	450	540	700	1,010	1,280	1,460	1,810	550	700	870	1,220	1,620	1,890	2,300
	1.0	460	580	730	1,010	1,350	1,570	1,920	590	730	970	1,310	1,630	2,020	2,510
	1.1	460	580	730	1,010	1,350	1,570	1,920	590	730	970	1,310	1,630	2,020	2,510
9	1.0	460	580	730	1,010	1,350	1,570	1,920	590	730	970	1,310	1,630	2,020	2,510
	1.2	500	610	810	1,100	1,360	1,690	2,100	640	780	1,060	1,430	1,890	2,170	2,720
	1.3	500	610	810	1,100	1,360	1,690	2,100	640	780	1,060	1,430	1,890	2,170	2,720
10	1.0	500	610	810	1,100	1,360	1,690	2,100	640	780	1,060	1,430	1,890	2,170	2,720
	1.2	540	640	880	1,190	1,570	1,810	2,270	700	830	1,140	1,540	2,020	2,170	2,790
	1.4	540	640	880	1,190	1,570	1,810	2,270	700	830	1,140	1,540	2,020	2,170	2,790
11	1.0	560	660	920	1,240	1,630	1,810	2,270	710	850	1,180	1,580	2,100	2,230	2,860
	1.2	560	680	920	1,240	1,660	1,810	2,290	710	850	1,180	1,580	2,100	2,230	2,860
	1.4	560	700	920	1,240	1,690	1,810	2,320	710	850	1,180	1,580	2,100	2,230	2,860
12	1.0	580	700	950	1,280	1,690	1,810	2,320	730	870	1,220	1,620	2,170	2,300	2,930
	1.2	580	700	950	1,280	1,690	1,810	2,320	730	870	1,220	1,620	2,170	2,300	2,930
	1.4	610	730	1,010	1,350	1,810	1,920	2,450	730	910	1,220	1,630	2,170	2,510	3,140
13	1.0	610	730	1,010	1,350	1,810	1,920	2,450	730	910	1,220	1,630	2,170	2,510	3,140
	1.2	610	750	1,010	1,350	1,810	2,010	2,510	750	910	1,270	1,680	2,240	2,620	3,240
	1.4	610	750	1,010	1,350	1,810	2,010	2,560	750	910	1,270	1,680	2,240	2,620	3,240
14	1.0	610	750	1,010	1,350	1,810	2,010	2,560	750	910	1,270	1,680	2,240	2,620	3,240
	1.2	610	770	1,010	1,360	1,810	2,100	2,620	780	910	1,310	1,750	2,300	2,720	3,340
	1.4	610	770	1,010	1,360	1,810	2,100	2,620	780	910	1,310	1,750			