


入れ子止め用スペーサ

入れ子止め



- 平行タイプ -

RoHS 10



型式	材質	硬度
ICSS	SKS3	53~56HRC
ICHS	HPM2T相当	37~41HRC

型式	材質	硬度
IUSS	SKS3	53~56HRC
IUHS	HPM2T相当	37~41HRC

RoHS 10

型式	材質	硬度
IPS	SKS3	53~56HRC

型式	T	L	A
Type	W	指定10mm単位	
ICSS (SKS3)	5	15	1
		20	
		25	
		30	
		35	
		40	
		45	
		50	
ICHS (HPM2T相当)	10	20	3
		25	
		30	
		35	
		40	
		45	
		50	
		60	
	10	70	5
		80	
		20	
		25	
		30	
		35	
		40	
		45	



型式	T	L	A	入れ子止め組み合わせ例 W-T
Type	W	指定10mm単位		
IUSS (SKS3)	5	20	1	10-20
	9	15		6-15
	10	20		10-20
IUHS (HPM2T相当)	10	25	3	10-25
		30		10-30
	12	15	5	8-15
		20		8-20
		25		8-25

Order 注文例

型式 - T - L - A
ICSS5 - 20 - L100 - A5


Delivery 出荷日 5 日目出荷

Example 使用例



Alterations 追加加工

型式 - T - L - A - (MC)
ICSS5 - 20 - L100 - A5 - MC

追加加工	記号	詳細												
	MC	W寸指定側にタップ加工します。												
		<table border="1"> <tr> <th>W</th> <th>M</th> </tr> <tr> <td>5</td> <td>3</td> </tr> <tr> <td>10</td> <td>5</td> </tr> </table> <table border="1"> <tr> <th>L</th> <th>ℓ</th> </tr> <tr> <td>30・40</td> <td>7.5</td> </tr> <tr> <td>50~100</td> <td>10</td> </tr> <tr> <td>110~180</td> <td>15</td> </tr> </table>	W	M	5	3	10	5	L	ℓ	30・40	7.5	50~100	10
W	M													
5	3													
10	5													
L	ℓ													
30・40	7.5													
50~100	10													
110~180	15													

ICSS・ICHSのみ適用

M	型式	T	L
	Type	W	指定5mm単位
5	IPS	8	20~40
6		10	
		15	
		20	
8		25	

Order 注文例


型式 - T - L
IPS 15 - 30 - 150



Delivery 出荷日 5 日目出荷

Example 使用例

Alterations 追加加工

型式 - T - L - (AVC・SRC)
IPS 15 - 30 - 150 - AVC-B100



追加加工	記号	詳細
	AVC	(エアベント加工) B=指定5mm単位 0 ≤ B ≤ L-5 指定方法 AVC-B100
	SRC	(スライドコア逃げ加工) B・C・D=指定5mm単位 0 ≤ B ≤ L-5, 5 ≤ D ≤ T/2 0 ≤ C ≤ L-5, B+C ≤ L-5 D < T-2M 指定方法 SRC-B30-C60-D10

AVCとSRCの併用は不可