


センターレール

—フリー指定タイプ—


RoHS




■取付ボルト穴2ヶ所



■取付ボルト穴3ヶ所



■取付ボルト穴4ヶ所



指示のない角部はC₀±1となります。

型式	材質	硬度
FCGS2M・FCGS3M・FCGS4M	SKS3	53~56HRC
FCGM2M・FCGM3M・FCGM4M	HPM2T相当	37~41HRC

■ボルト穴サイズ表

W	T	d1	d2	t1
12	10~30	8	4.5	5
	10~14	8	4.5	5
15	15~40	9.5	5.5	6
	15~24	11	6.5	7
20	25~50	14	9	9

型式 Type	W	T 指定1mm単位	L 指定5mm単位	ボルト穴ピッチ 指定0.5mm単位			
				A	B	C	D
FCGS2M (2穴) FCGS3M (3穴) FCGS4M (4穴) (SKS3)	12	10~30	40~100	6 ≤ A ≤ B - 10	A + 10 ≤ B ≤ C - 10	B + 10 ≤ C ≤ D - 10	C + 10 ≤ D ≤ L - 6
		10~14	40~100	6 ≤ A ≤ B - 10	A + 10 ≤ B ≤ C - 10	B + 10 ≤ C ≤ D - 10	C + 10 ≤ D ≤ L - 6
FCGM2M (2穴) FCGM3M (3穴) FCGM4M (4穴) (HPM2T相当)	20	15~40	40~150	7 ≤ A ≤ B - 11.5	A + 11.5 ≤ B ≤ C - 11.5	B + 11.5 ≤ C ≤ D - 11.5	C + 11.5 ≤ D ≤ L - 7
		15~24	40~150	7.5 ≤ A ≤ B - 13	A + 13 ≤ B ≤ C - 13	B + 13 ≤ C ≤ D - 13	C + 13 ≤ D ≤ L - 7.5
		25~50	40~150	9 ≤ A ≤ B - 16	A + 16 ≤ B ≤ C - 16	B + 16 ≤ C ≤ D - 16	C + 16 ≤ D ≤ L - 9

Order 注文例

型式	T	L	A	B	C	D
FCGS4M12	13	100	A13.0	B33.5	C54.5	D78.5

Delivery 出荷日 •FCGS□M **5** 日日出荷

•FCGM□M **5** 日日出荷 **ご注文締切** ストック B 3日日出荷 300円/1本 PM 8:00迄 P48

◎3本以上で1明細行当たり一律810円



Price 価格

■数量スライド価格 (◎1円未満切り捨て) P47

数量区分	標準対応	個別対応大口
数量	1~9	10~19
値引率	基準単価	5%
		20~
		お見積り

◎表示数量超えはWOSにてご確認ください。

W	T	¥基準単価 1~9本											
		L40~55		L60~75		L80~95		L100~115		L120~135		L140~150	
		FCGS□M	FCGM□M	FCGS□M	FCGM□M	FCGS□M	FCGM□M	FCGS□M	FCGM□M	FCGS□M	FCGM□M	FCGS□M	FCGM□M
12	10~14	4,530	4,500	5,170	5,130	5,460	5,410	6,040	5,980				
	15~20	4,600	4,550	5,270	5,210	5,570	5,510	6,150	6,090				
	21~30	4,710	4,660	5,430	5,340	5,780	5,670	6,370	6,250				
15	10~14	4,790	4,660	5,350	5,300	5,660	5,610	6,250	6,170				
	15~20	4,890	4,730	5,460	5,410	5,810	5,720	6,390	6,300				
	21~30	5,080	4,850	5,660	5,560	6,050	5,890	6,630	6,470				
20	31~40	5,340	5,180	5,980	5,910	6,330	6,250	6,970	6,890				
	15~20	5,210	5,090	5,590	5,410	6,230	5,820	7,060	6,780	7,350	7,210	8,010	7,640
	21~30	5,490	5,190	5,650	5,550	6,410	6,010	7,190	7,010	7,650	7,480	8,150	7,930
	31~40	5,660	5,530	6,050	5,880	6,550	6,310	7,640	7,350	8,130	7,800	8,630	8,250
	41~50	6,300	6,130	6,770	6,520	7,330	7,010	8,540	8,170	9,110	8,660	9,690	9,190



Example 使用例

