

FIXING KEYS FOR PUNCHES WITH KEY GROOVES キー溝付パンチ用固定キー

KEYS 廻り止めキー

RoHS10

型式	M 材質	H 硬度	S 表面処理
PSKB	S45C	45~55HRC	—
PSKBH	SKS3	58~62HRC	クロメート処理(銀色)

ボルト	D	d	T	型式	
				Type	No.
M4	10	4.2	3	PSKB	4
					4-4.5
					5
M5	12	5.2	4.5		5-4.5
					6
					6-4.5
M4	10	4.2	3	PSKBH	4
					4-4.5
					5
M5	12	5.2	4.5		5-4.5
					6
					6-4.5

RoHS10

型式	M 材質	H 硬度
PSKS	S45C	45~55HRC
PSKJ	SKS3	58~62HRC

ボルト	D	d	t	型式	
				Type	No.
M4	10	4.5	2.5	PSKS	4
M5	13	5.5	3	PSKS	5
M4	12	4.2	2.5	PSKJ	4
M5	15	5.2	3	PSKJ	5

RoHS10

型式	M 材質	H 硬度	S 表面処理
PSK	S45C	45~55HRC	—
PSKP	SKS3	58~62HRC	クロメート処理(銀色)

ボルト	A	B	C	d	T	型式	
						Type	No.
M4	10	11	6	4.2	3	PSK	4-3
							4
							5-3
M5	13	5.5	3	4.5	4.5		5
							6-3
							6
M6	12	14	7	6.2	3	6-3	
						4	
						5-3	
M4	11	11	5.5	4.2	3	PSKP	4-3
							4
							5-3
M5	13	5.5	3	4.5	4.5		5
							6-3
							6
M6	14	14	7	6.2	3	6-3	
						4	
						5-3	
M4	10	11	6	4.2	3	PSKH	4-3
							4
							5-3
M5	13	5.5	3	4.5	4.5		5
							6-3
							6

PSKPは形状の中心に穴が空いている為、取付の方向を選びません。

RoHS10 PSKW (ロングタイプ)

M 材質 S45C
H 硬度 45~55HRC

ボルト	B	C	d	P				型式		T (選択)	A 指定1mm単位
				A=21~30	A=31~40	A=41~50	A=51~60	Type	No.		
M4	11	6	4.2	10	20	30	—	PSKW	4	3	21~50
M5				—	20	30	40		5		

Order 注文例

型式 - T - A
PSKB 4
PSKS 5
PSKP 5
PSKW 4 - 3 - 40

Delivery 出荷日

在庫品

3 日日出荷

ストーク A

Example 使用例

RoHS10 KE

M 材質 S45C
H 硬度 45~55HRC

型式	
Type	L
KE	8
	10
	12
	15
	20
	25
30	

Order 注文例

型式 KE 12

Delivery 出荷日

在庫品

Example 使用例

RoHS10 KED KES KEG

L	公差
最短~10	0
11~18	-0.15
19~30	-0.18
31~50	-0.21
51~80	-0.25
81~110	-0.30
	-0.35

JIS B 1301-1996

Type	材質
KED	S45C
KES	
KEG	

引張強さ 600N/mm²以上

型式	Type	Bh9	L											H許公差		C				
			2	3	4	5	6	7	8	9	10	11	0	0						
KED KES KEG	2	0	10	15	20											2	0	0.16~0.25		
	3	-0.025	10	15	20	25	30									3	-0.025			
	4	0	10	12	15	16	18	20	25	30	35	40	45	50		4	0			
	5	-0.030	10	12	15	16	18	20	25	30	35	40	45	50		5	0	0.25~0.40		
	6	0	10	12	15	16	18	20	25	30	35	40	45	50	55	60	6		0	
	7	-0.036	15	18	20	25	30	35	40	45	50	55	60	70	80		7		0	
	8	0	15	16	18	20	25	30	35	40	45	50	55	60	70	80		8	0	0.40~0.60
	10	-0.043	15	18	20	25	30	35	40	45	50	55	60	70	80		9	-0.090		
	12	0	20	25	30	35	40	45	50	55	60	70	80	90		10	0			
	14	0	30	35	40	45	50	55	60	70	80	90								
	15	-0.043	30	35	40	45	50	55	60	70	80	90								
	16	0	40	45	50	55	60	70	80	90	100									
	18	0	40	45	50	55	60	70	80	90	100	110				11	0			

Order 注文例

型式 - L
KED 6 - 30

Delivery 出荷日

在庫品

Alterations 追加加工

型式 - L(LC)
KED 6 - LC28

3 日日出荷

ストーク T
ストーク A

全長	追加工	記号	詳細	
			LC=指定1mm単位	
全長	全長変更	LC	B	LC範囲
			2	5~20
			3	6~30
			4	8~50
			5	8~50
			6	10~60
			7	15~80
			8	15~80
			10	15~80
			12	20~90
			14	20~90
			15	25~90
			16	35~100
			18	35~110